




Connectors > PCB Connectors > Backplane Connectors > High Speed Backplane Connectors



Number of Positions: 120
Row-to-Row Spacing: 2.5 mm [.098 in]
Mating Alignment: With
Mating Alignment Type: Guide Slot
Number of Rows: 15

Features

Product Type Features

Signal Arrangement	Differential
Connector & Contact Terminates To	Printed Circuit Board
Connector System	Board-to-Board
Backplane Module Type	Right
PCB Connector Type	PCB Mount Header
Shroud Style	Partially Shrouded

Configuration Features

Number of Pairs	40
Number of Signal Positions	80
Backplane Architecture	Traditional Backplane
Stackable	No
Pairs per Column	5
Number of Positions	120
Number of Rows	15
Number of Columns	8



PCB Mount Orientation	Vertical
Electrical Characteristics	
Operating Voltage	250 VAC
Impedance	100 Ω
Signal Characteristics	
Data Rate	10 Gb/s
Differential Impedance	100 Ω
Number of Differential Pairs per Column	5
Body Features	
Primary Product Color	Black
Contact Features	
PCB Contact Termination Area Plating Material Finish	Matte
Contact Mating Area Plating Material Thickness	.76 μm[29.92 μin]
PCB Contact Termination Area Plating Material Thickness	.5 μm[20 μin]
Contact Shape & Form	Rectangular
Contact Mating Area Plating Material	Gold (Au)
Contact Mating Area Length	6 mm[.236 in]
Contact Base Material	Phosphor Bronze
PCB Contact Termination Area Plating Material	Tin
Contact Type	Pin
Contact Current Rating (Max)	.5 A
Termination Features	
Termination Method to PCB	Through Hole - Press-Fit
Termination Post & Tail Length	2.5 mm[.098 in]
Mechanical Attachment	
Guide Hardware	Without
PCB Mount Retention	With
Mating Retention	Without
PCB Mount Retention Type	Action/Compliant Tail
PCB Mount Alignment	Without
Mating Alignment	With
Mating Alignment Type	Guide Slot



Connector Mounting Type	Board Mount
Housing Features	
Number of Shrouded Sides	3
End Wall Location	Right
Housing Material	LCP (Liquid Crystal Polymer)
Centerline (Pitch)	1.9 mm[.075 in]
Dimensions	
Connector Width	24.4 mm
Connector Height	11.8 mm
PCB Hole Diameter	.47 mm
Connector Length	15.35 mm
Row-to-Row Spacing	2.5 mm[.098 in]
Usage Conditions	
Operating Temperature Range	-65 – 90 °C[-85 – 194 °F]
Operation/Application	
Circuit Application	Signal
Industry Standards	
Compatible With Agency/Standards Products	UL
UL Flammability Rating	UL 94V-0
Compatible With Approved Standards Products	UL E28476
Packaging Features	
Packaging Method	Box & Tube, Tube
Product Compliance	
For compliance documentation, visit the product page on TE.com>	
EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC



Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1934218-1
Tin Man Recept Assy 5 pair 8 Column


Also in the Series | Z-PACK TinMan



High Speed Backplane Connectors(68)

Customers Also Bought






TE Part #3-1589472-4
STL015PC2DC036N = WDUALOBE



TE Part #1934350-1
TinMan R/A Header Assy 5x8 Dou



TE Part #1-1462050-6
HF3 02 = 75OHM 140MW 4.5V MONO



TE Part #462481-000
55PC0221-18-6/9



TE Part #1-5645501-2
SKT MS S4 BN SN-SN 10M W/SEAL




TE Part #2-1658013-2
MSB0.80PL5ASY080FL,-,10,-TY



TE Part #1934272-1
Tin Man Header Assy 5x8 left



TE Part #2-1617019-0
FW1105G00 = 2020-FW RELAY



TE Part #6469083-2
HMZD 3PAIR, HDR ASSY, 25MM MOD



TE Part #5415406-2
TEST PLUG, RTANG, PCB, G

Documents

Product Drawings

Tin Man Header Assy 5x8 Left

English

CAD Files

Customer View Model

ENG_CVM_1934273-1_B.3d_igs.zip

English

Customer View Model

ENG_CVM_1934273-1_B.3d_stp.zip

English

Customer View Model

ENG_CVM_1934273-1_B.2d_dxf.zip

English

3D PDF

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages



[High Speed Backplane Connectors catalog - Z-PACK TinMan High Speed, High Density Backplane Connector](#)

English

[Z-PACK TinMan High Speed High Density Backplane Connector Catalog 5-1773447-9](#)

English

[Product Specifications](#)

[Application Specification](#)

English