

Chainsaw XGT®

UC011G

40Vmax • 0 - 25,5 m/s • 35 cm / 14"

Efficient brushless saw with a high chain speed for heavy-duty use

XGT® 40Vmax battery powered chainsaw. A very high powered chainsaw made for professionals. equivalent to 42 cc class engine chain saw. This chainsaw is perfect for construction sites, gardens or summer cottages.



Technical specifications

Voltage XGT	✓
Nominal Battery Voltage	40 V
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Max. Chain Speed (No Load)	25,5 m/s
chain bar length	350 mm (14")
Chain Pitch	3/8 / 0,325 "
Chain Gauge	0,043 / 0,050 "
Chain Gauge	1,1 / 1,3 mm
Number of Drive Links	52 / 59
Chain Oil Tank	260 ml
Brushless Motor	✓
Vibration Level, Cutting Wood	4,4 m/s ²
Vibration Uncertainty (K Factor), Cutting Wood	1,5 m/s ²
Sound Pressure Level (L _{pA})	94 dB(A)
Sound Power Level (L _{WA})	102 dB(A)

User benefits

- Lightweight for reduced operator fatigue
- Large oil filling port with view window allows operator to easily add and check bar oil level
- Main power switch with auto power-off function for battery saving and avoiding unintentional start up
- eXtreme Protection Technology (XPT) is engineered for improved dust and water resistance for operation in harsh conditions
- Adjustable automatic chain lubrication with large oil reservoir
- Captive nuts to prevent loss of nuts when replacing guide bar or saw chain

Link to product - www.makitauk.com



Related products

Optional AC

191T87-4

Guide bar 14" / 35 cm, 1,1 mm



191T91-3

Saw chain 80TXL, 14" / 35 cm, 1,1



419288-5

Chain Protection Cover 14" / 35 cm



782023-7

Wrench 13 -16



Other

User manual

Parts drawing