

Eaton EBF3330W1

Catalog Number: EBF3330W1

Eaton Bussmann series low voltage NH fuse base, Fuse rail, low voltage, 630 A, AC 690 V, NH3, 3P, IEC, 185 mm busbar, 2-V
Terminals with double V-clamps



General specifications

Product Name	Catalog Number
Eaton Bussmann series low voltage NH fuse base	EBF3330W1
	EAN
	5027590336574
Product Length/Depth	Product Height
715 mm	190 mm
Product Width	Product Weight
103 mm	4051 g
Compliances	Certifications
CE	IEC 60269-1
	IEC 60269-2

Product specifications

Type

Fuse accessory

Application

Transformers substations, distribution boards, feeder pillars, cable distribution cabinets

Amperage Rating

630 A

Rated permanent current (Iu)

630 A

Conditioned rated short-circuit current Iq

0.1 kA

Double interrupting

No

Number of poles

Three-pole

Construction size (fuse inserts)

NH3

Distance

Between rail center: 185 mm

Electrical connection type of main circuit

Cable clamp

Construction size

NH3

Fuse shape

Vertical

Release indication

None

Suitable for

NH3

Suitable for fuses

NH3

Mounting method

Busbar

Voltage rating

690

Resources

Brochures

[eaton-bussmann-series-ebf-vertical-fuse-rail-datasheet-10240en-us.pdf](#)

Catalogs

[eaton-product-overview-for-machinery-catalogue-ca08103003zen-en-us.pdf](#)

[CA134002EN](#)

Declarations of conformity

[UKCA Vertical NH fuse rails for NH fuse-links sizes 00 to 3](#)

[CE Vertical NH fuse rails for NH fuse-links sizes 00 to 3](#)

Technical data sheets

[10275 EBV Vertical fuse switch-disconnector](#)

Technical service bulletins

[10293 EBH Horizontal switch-disconnector](#)

Electrical connection type

Cable clamp

Model

Fuse base

Rated operating voltage (Ue) at AC - max

690 V



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia