

## FEATURES

- **Graphite material:** Offers excellent thermal conductivity and chemical resistance, ensuring durability in harsh conditions
- **Maximum operating pressure of 20000 kPa:** Suitable for high-pressure applications, enhancing safety and reliability
- **Maximum operating temperature of 650 °C:** Capable of withstanding extreme temperatures, making it versatile for various industrial uses
- **Rotary speed of 30 m/s:** Supports high-speed operations, reducing wear and tear
- **8 mm section:** Provides a robust seal, minimizing leakage and maintenance

## RS PRO 8mm Graphite Gland Packing, 20000 kPa

RS Stock No: 606-572



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

This RS PRO 8mm graphite gland packing is designed for high-pressure and high-temperature sealing applications. It is ideal for use in pumps and valves, providing reliable performance in demanding industrial environments.

## General Specifications

Maximum Operating Pressure	20000 kPa
Product Type	Gland & Valve Packing
Rotary Speed	30 m/s
Section	8 mm
Sub Type	Gland Packing

## Mechanical Specifications

Length	8 m
Material	Graphite

## Operation Environment Specifications

Maximum Operating Temperature	650 °C
-------------------------------	--------

## Approvals

Standards/Approvals	ANSI-ESD S20.20:2021, RoHS
---------------------	----------------------------