## **mole**x

### PRODUCT SPECIFICATION

#### 1.0 SCOPE

This Product Specification covers 2.54 mm centerline (pitch) 0.64 mm square pin headers when mated with either printed circuit board (PCB) connectors or connectors terminated with 22 to 30 AWG wire using crimp technology.

#### 2.0 PRODUCT DESCRIPTION

#### 2.1 PRODUCT NAME AND SERIES NUMBERS

Crimp Terminals: 4809, 2759, 41572, 6459, 8088

Crimp Housings: 2695 PCB Connectors: 4455 Headers: 6410, 7395

Other products conforming to this specification are noted on the individual drawings.

#### 2.2 DIMENSIONS, MATERIALS, PLATINGS AND MARKINGS

Terminal Material: Brass or Phos. Bronze (for Max performance use phos bronze material.)

Housing: Nylon or Polyester Pins: Brass or Phos. Bronze

For more information on dimensions, materials, and plating see the individual drawings.

#### 2.3 SAFETY AGENCY APPROVALS

UL File Number ...... E29179 CSA ......LR19980

	Agency Voltage Rating Agency Co			Agency	
OFDIFO	(AC RMS or	DC)	Rating	` •	Temperature
SERIES			Circuit)	(Amps)	Rating (°C)
	UL	CSA	UL	CSA	UL
2695	500 V AC	250	-	2.5	105°C
	600 V DC				
4455	600 V AC/DC	250	-	2.5	105°C
6410	600 V AC/DC	250	-	2.5	105°C
7395	600 V AC/DC	250	-	4	105°C

#### 3.0 APPLICABLE DOCUMENTS AND SPECIFICATIONS

None

#### 4.0 RATINGS

#### 4.1 VOLTAGE

500 Volts AC (or 600 Volts DC)

DEVICION. FOR/ECNINEODMATION. TITLE.

<b>G</b>	EC No: 113831  DATE: 23/02/2017		JCT SPECIFICATION  NTER KK CONNE	_	1 of 6
DOCUMEN <sup>*</sup>	T NUMBER:	CREATED / REVISED BY:	CHECKED BY:	APPRO\	/ED BY:
PS-99020-0088		SS06	SS06	ISHW	ARG
	TEMPLATE FILENAME: PRODUCT SPECISIZE AIV.1).DOC				

# molex

### PRODUCT SPECIFICATION

**4.2 CURRENT AND APPLICABLE WIRES** (Current is dependent on connector size, contact material, plating, ambient temperature, printed circuit board characteristics and related factors. Actual current rating is application dependent and should be evaluated for each application.)

AWG	Amps (Max)	Outside Insulation Diameter
22	4.00	See Drawings
24	3.75	See Drawings
26	3.50	See Drawings
28	3.00	See Drawings
30	2.50	See Drawings

Note: current ratings are for a single circuit, based on not exceeding 30°C temperature rise.

4.3 TEMPERATURE (ambient + 30°C temp rise)

	Brass Terminals	Phos Bronze Terminals
Operating Temperature	-40°C to +80°C*	-40°C to +105°C*
Non-Operating Temperature	-40°C to +105°C**	-40°C to +105°C

<sup>\*</sup>including terminal temperature rise.

G REVISION:	EC No: 113831  DATE: 23/02/2017		JCT SPECIFICATION  NTER KK CONNE	_	2 of 6
DOCUMEN <sup>T</sup>	T NUMBER:	CREATED / REVISED BY:	CHECKED BY:	APPRO\	/ED BY:
PS-99020-0088		SS06	SS06	ISHW	ARG
	TEMPLATE FILENAME: PRODUCT SPECISIZE A](V.1).DOC				

<sup>\*\*</sup>parts not mated

# molex®

### PRODUCT SPECIFICATION

#### **5.0 PERFORMANCE**

#### **5.1 ELECTRICAL REQUIREMENTS**

DESCRIPTION	TEST CONDITION	REQUIREMENT
Contact Resistance (Low Level)	Mate connectors: apply a maximum voltage of 20 mV and a current of 100 mA.	10 milliohms MAXIMUM [initial]
Contact Resistance of Wire Termination (Low Level)	Terminate the applicable wire to the terminal and measure wire using a voltage of 20 mV and a current of 100 mA.	2 milliohms MAXIMUM [initial]
Insulation Resistance	Unmate & unmount connectors: apply a voltage of 500 VDC between adjacent terminals and between terminals to ground.	1000 Megaohms MINIMUM
Dielectric Withstanding Voltage	Unmate connectors: apply a voltage of {two times the rated voltage plus 1000 volts} VAC for 1 minute between adjacent terminals and between terminals to ground.	No breakdown
Capacitance	Measure between adjacent terminals at 1 MHz.	2 picofarads MAXIMUM
Temperature Rise (via Current Cycling)	Mate connectors: measure the temperature rise at the rated current after:  1) 96 hours (steady state)  2) 240 hours (45 minutes ON and 15 minutes OFF per hour)  3) 96 hours (steady state)	Temperature rise: +30°C MAXIMUM

REVISION:   ECR/ECN INFORMATION:		JCT SPECIFICATI NTER KK CONNE	_	3 of 6
DOCUMENT NUMBER:	CREATED / REVISED BY:	CHECKED BY:	<u>APPROV</u>	/ED BY:
PS-99020-0088	SS06	SS06	ISHW	ARG
TEMPLATE FILENAME: PRODUCT_SPEC(SIZE_A](V.1).DOC				[SIZE_A](V.1).DOC

# molex®

### PRODUCT SPECIFICATION

#### **5.2 MECHANICAL REQUIREMENTS**

DESCRIPTION	TEST CONDITION	REQUIREMENT
Connector Mate and Unmate Forces	Per circuit when mated to a 0.635mm Sq. pin header without friction lock.  Mate and unmate connector (male to female) at a rate of 25 ± 6 mm per minute.	4.9 N MAXIMUM insertion force & 0.56 N MINIMUM withdrawal force
Terminal Retention Force (in Housing)	Axial pullout force on the terminal in the housing at a rate of 25 ± 6 mm per minute. (Forces will change with platings and materials.)	17.8 N MINIMUM withdrawal force
Terminal Insertion Force (into Housing)	Apply an axial insertion force on the terminal at a rate of 25 ± 6 mm. (Forces will change with platings and materials.)	6.67 N MAXIMUM insertion force
Durability	Mate connectors up to 25 cycles at a maximum rate of 10 cycles per minute prior to Environmental Tests.	10 milliohms MAXIMUM (change from initial)
Vibration (Random)	Mate connectors and vibrate per EIA 364-28, test condition VII.	10 milliohms MAXIMUM (change from initial) & Discontinuity < 1 microsecond
Shock (Mechanical)	Mate connectors and shock at 50 g's with ½ sine wave (11 milliseconds) shocks in the ±X,±Y,±Z axes (18 shocks total).	10 milliohms MAXIMUM (change from initial]) & Discontinuity < 1 microsecond
Wire Pullout Force (Axial)	Apply an axial pullout force on the wire at a rate of 25 ± 6 mm. (For maximum performance use Molex application tooling with stranded tinned copper wire)	Wire pullout force depends on crimp tooling. See relevant Molex Application Tooling Specification for requirements.
Normal Force	Apply a perpendicular force.	2.94 N (300 grams) average

REVISION:   ECR/ECN INFORMATION:		JCT SPECIFICATION  NTER KK CONNE	_	4 of 6
DOCUMENT NUMBER:	CREATED / REVISED BY:	CHECKED BY:	<u>APPROV</u>	/ED BY:
PS-99020-0088	SS06	SS06	ISHW	ARG
TEMPLATE FILENAME: PRODUCT_SPEC[SIZE_A](V.1).DOC				[SIZE_A](V.1).DOC

## $\widehat{\text{molex}}^{\circ}$

### PRODUCT SPECIFICATION

#### **5.3 ENVIRONMENTAL REQUIREMENTS**

DESCRIPTION	TEST CONDITION	REQUIREMENT
Shock (Thermal)	Mate connectors; expose to 5 cycles of:         Temperature °C       Duration (Minutes)         -40 +0/-3       30         +25 ±10       5 MAXIMUM         +105 +3/-0       30         +25 ±10       5 MAXIMUM	10 milliohms MAXIMUM (change from initial) & Visual: No Damage
Thermal Aging	Mate connectors; expose to: 96 hours at 105 ± 2°C	10 milliohms MAXIMUM (change from initial]) & Visual: No Damage
Humidity (Steady State)	Mate connectors: expose to a temperature of 40 ± 2°C with a relative humidity of 90-95% for 96 hours.  Note: Remove surface moisture and air dry for 1 hour prior to measurements.	10 milliohms MAXIMUM (change from initial) & Dielectric Withstanding Voltage: No Breakdown at 500 VAC & Insulation Resistance: 1000 Megaohms MINIMUM & Visual: No Damage
Humidity (Cyclic)	Mate connectors: cycle per EIA-364-31: 24 cycles at temperature 25 ± 3°C at 80 ± 5% relative humidity and 65 ± 3°C at 50 ± 5% relative humidity; dwell time of 1.0 hour; ramp time of 0.5 hours.  {Note: Remove surface moisture and air dry for 1 hour prior to measurements.}	10 milliohms MAXIMUM (change from initial) & Dielectric Withstanding Voltage: No Breakdown at 500 VAC & Insulation Resistance: 1000 Megaohms MINIMUM & Visual: No Damage
Solderability	Per SMES-152	Solder coverage: 95% MINIMUM (per SMES-152)

G REVISION:	ECR/ECN INFORMATION:  EC No: 113831  DATE: 23/02/2017		JCT SPECIFICATION  NTER KK CONNE	_	5 of 6
DOCUMENT NUMBER:		CREATED / REVISED BY:	CHECKED BY:	APPRO\	/ED BY:
PS-99020-0088		SS06	SS06	ISHW	ARG
	TEMPLATE FILENAME: PRODUCT_SPEC[SIZE_A](V.1).DOC				

# molex®

### PRODUCT SPECIFICATION

#### **5.3 ENVIRONMENTAL REQUIREMENTS**

DESCRIPTION	TEST CONDITION	REQUIREMENT
Solder Resistance	Dip connector terminal tails in solder: Solder Duration: 5 ± 0.5 seconds; Solder Temperature: 230 ± 5°C	Visual: No Damage to insulator material
Cold Resistance	Mate connectors: Duration: 96 hours; Temperature: -40 ± 3°C	10 milliohms MAXIMUM (change from initial) & Visual: No Damage
Corrosive Atmosphere: Flowing Mixed Gas (FMG)	Test per EIA-364-65, Class II, Exposure to gasses for 4 days, unmated.	10 milliohms MAXIMUM (change from initial) & Visual: No Damage

#### 6.0 PACKAGING

Parts shall be packaged to protect against damage during handling, transit and storage.

#### 7.0 GAGES AND FIXTURES

8.0 OTHER

G REVISION:	ECR/ECN INFORMATION: EC No: 113831  DATE: 23/02/2017	PRODUCT SPECIFICATION 2.54mm CENTER KK CONNECTORS			6 of 6
DOCUMENT NUMBER:		CREATED / REVISED BY:	CHECKED BY:	APPROVED BY:	
PS-99020-0088		SS06	SS06	ISHWARG	
TEMPLATE FILENAME: PRODUCT_SPEC[SIZE_A](V.1).DOC					