

Miniature circuit-breaker, Acti9 iC40N, 1P+N, 25 A, B curve, 6000 A (IEC 60898-1), 10 kA (IEC 60947-2)

A9P44625

EAN Code: 3606481324559

Main

Range	Acti9	
product name	Acti9 iC40	
Product or component type	Miniature circuit-breaker	
Device short name	iC40N	
Device application	Distribution	
Poles description	1P + N	
Number of protected poles	1	
Neutral position	Left	
[In] rated current	25 A	
Network type	AC	
Trip unit technology	Thermal-magnetic	
Curve code	В	
Breaking capacity	10 kA Icu at 230 V AC 50/60 Hz conforming to EN/IEC 60947-2 6000 A Icn at 230 V AC 50/60 Hz conforming to EN/IEC 60898-1	
Suitability for isolation	Yes conforming to EN/IEC 60947-2	
Quality labels	IMQ KEMA OVE	

Complementary

Network frequency	50/60 Hz	
[Ue] rated operational voltage	230 V AC 50/60 Hz	
Magnetic tripping limit	35 x In conforming to EN/IEC 60898-1 4 x In +/- 20 % conforming to EN/IEC 60947-2	
[Ics] rated service breaking capacity	6000 A 100 % x Icn at 230 V AC 50/60 Hz conforming to EN/IEC 60898-1 7.5 kA 75 % x Icn at 230 V AC 50/60 Hz conforming to EN/IEC 60947-2	
Limitation class	3 conforming to EN/IEC 60898-1	
[Ui] rated insulation voltage	400 V AC 50/60 Hz conforming to EN/IEC 60947-2	
[Uimp] rated impulse withstand voltage	4 kV conforming to EN/IEC 60947-2	
Contact position indicator	Yes	
control type	Toggle	
Local signalling	ON/OFF indication Trip indicator	
Mounting mode	Clip-on	

Mounting support	DIN rail
9 mm pitches	2
Height	85 mm
Width	18 mm
Depth	74 mm
Product weight	120 g
Colour	White
Mechanical durability	20000 cycles
Electrical durability	10000 cycles
Locking options description	Padlocking device
Connections - terminals	Tunnel type terminals top or bottom 110 mm² flexible Tunnel type terminals top or bottom 116 mm² rigid
Wire stripping length	14 mm for top or bottom connection
Tightening torque	2 N.m top or bottom
Earth-leakage protection	Separate block

Environment

Standards	EN/IEC 60898-1
	EN/IEC 60947-2
Product certifications	CE
	BV
	RINA
	DNV
IP degree of protection	IP20 conforming to IEC 60529
	IP40 (modular enclosure) conforming to IEC 60529
Pollution degree	3 conforming to EN/IEC 60947-2
Relative humidity	95 % at 55 °C
Operating altitude	2000 m
Ambient air temperature for operation	-2570 °C
Ambient air temperature for storage	-4085 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.8 cm
Package 1 Width	7.4 cm
Package 1 Length	9.4 cm
Package 1 Weight	120.0 g
Unit Type of Package 2	BB1
Number of Units in Package 2	12
Package 2 Height	8.0 cm
Package 2 Width	9.8 cm
Package 2 Length	22.5 cm
Package 2 Weight	1.51 kg

Unit Type of Package 3	S03
Number of Units in Package 3	132
Package 3 Height	30.0 cm
Package 3 Width	30.0 cm
Package 3 Length	40.0 cm
Package 3 Weight	17.02 kg

Logistical informations

Country of origin

Contractual warranty

Warranty 18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

Carbon footprint (kg.eq.CO2 per CR, Total Life cycle)	24
Environmental Disclosure	Product Environmental Profile

Use Better

Materials and Substances		
Packaging made with recycled cardboard	Yes	
Packaging without single use plastic	Yes	
EU RoHS Directive	Compliant with Exemptions	
SCIP Number	C839c050-8547-41ce-b0db-e9813554fc09	
REACh Regulation	REACh Declaration	

Use Again

○ Repack and remanufacture	
Circularity Profile	No need of specific recycling operations
Take-back	No
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins