


# TA3603



## Temperature transmitter

TA-025F3EN14-A-ZVG/US



### Product characteristics

|                              |                                              |            |
|------------------------------|----------------------------------------------|------------|
| Number of inputs and outputs | Number of analogue outputs: 1                |            |
| Measuring range              | -18...149 °C                                 | 0...300 °F |
| Process connection           | threaded connection 1/4" NPT external thread |            |
| Installation length EL [mm]  | 25                                           |            |

### Application

|                       |                                         |  |
|-----------------------|-----------------------------------------|--|
| Special feature       | Gold-plated contacts                    |  |
| Measuring element     | 1 x Pt 1000; (to DIN EN 60751, class A) |  |
| Media                 | liquids and gases                       |  |
| Pressure rating [bar] | 400                                     |  |

### Electrical data

|                             |            |  |
|-----------------------------|------------|--|
| Operating voltage [V]       | 10...30 DC |  |
| Current consumption [mA]    | < 30       |  |
| Protection class            | III        |  |
| Reverse polarity protection | yes        |  |

### Inputs / outputs

|                              |                               |  |
|------------------------------|-------------------------------|--|
| Number of inputs and outputs | Number of analogue outputs: 1 |  |
|------------------------------|-------------------------------|--|

### Outputs

|                              |                                                 |  |
|------------------------------|-------------------------------------------------|--|
| Total number of outputs      | 1                                               |  |
| Output signal                | analogue signal                                 |  |
| Number of analogue outputs   | 1                                               |  |
| Analogue current output [mA] | 4...20                                          |  |
| Max. load [Ω]                | (U <sub>b</sub> - 8,5 V) / 21,5 mA; 24 V: 720 Ω |  |
| Short-circuit protection     | yes                                             |  |
| Overload protection          | yes                                             |  |

### Measuring/setting range

|                     |              |            |
|---------------------|--------------|------------|
| Probe length L [mm] | 15.5         |            |
| Measuring range     | -18...149 °C | 0...300 °F |

### Resolution

|                                   |      |  |
|-----------------------------------|------|--|
| Resolution of analogue output [K] | 0.04 |  |
|-----------------------------------|------|--|

# TA3603



## Temperature transmitter

TA-025F3EN14-A-ZVG/US

| Accuracy / deviations                                                               |                        |                                                                                     |
|-------------------------------------------------------------------------------------|------------------------|-------------------------------------------------------------------------------------|
| Precision analogue output                                                           | [K]                    | $\pm 0,3 + (\pm 0,1 \% \text{ MS})$                                                 |
| Temperature coefficient                                                             | [% of the span / 10 K] | 0,1; (in case of deviation from the reference condition $25 \pm 5^\circ \text{C}$ ) |
| Response times                                                                      |                        |                                                                                     |
| Dynamic response T05 / T09                                                          | [s]                    | 1 / 3; (to DIN EN 60751)                                                            |
| Operating conditions                                                                |                        |                                                                                     |
| Ambient temperature                                                                 | [°C]                   | -40...100                                                                           |
| Storage temperature                                                                 | [°C]                   | -40...100                                                                           |
| Protection                                                                          |                        | IP 68; IP 69K                                                                       |
| Tests / approvals                                                                   |                        |                                                                                     |
| EMC                                                                                 | DIN EN 61000-6-2       |                                                                                     |
|                                                                                     | DIN EN 61000-6-3       |                                                                                     |
| Shock resistance                                                                    | DIN EN 60068-2-27      | 50 g (11 ms)                                                                        |
| Vibration resistance                                                                | DIN EN 60068-2-6       | 20 g (10...2000 Hz)                                                                 |
| MTTF                                                                                | [years]                | 1092                                                                                |
| UL approval                                                                         | power supply           | Class 2                                                                             |
|                                                                                     | UL Approval no.        | K005                                                                                |
|                                                                                     | File number UL         | E217884                                                                             |
| Mechanical data                                                                     |                        |                                                                                     |
| Weight                                                                              | [g]                    | 89.2                                                                                |
| Housing                                                                             |                        | cylindrical                                                                         |
| Dimensions                                                                          | [mm]                   | $\varnothing 18.8 / L = 85.8$                                                       |
| Materials                                                                           |                        | stainless steel (316L/1.4404); PEI; FKM                                             |
| Materials (wetted parts)                                                            |                        | stainless steel (316L/1.4404)                                                       |
| Process connection                                                                  |                        | threaded connection 1/4" NPT external thread                                        |
| Probe diameter                                                                      | [mm]                   | 6                                                                                   |
| Installation length EL                                                              | [mm]                   | 25                                                                                  |
| Remarks                                                                             |                        |                                                                                     |
| Remarks                                                                             |                        | The values for accuracy apply to flowing water.                                     |
| Pack quantity                                                                       |                        | 1 pcs.                                                                              |
| Electrical connection                                                               |                        |                                                                                     |
| Connector: 1 x M12; coding: A; Contacts: gold-plated                                |                        |                                                                                     |
|  |                        |                                                                                     |




# TA3603

## Temperature transmitter

TA-025F3EN14-A-ZVG/US



### Connection



OUT:                   analogue output  
                          colours to DIN EN 60947-5-2