

# ATB Adjustable Breaking Torque Wrenches

## ATB 25, 50 & 100

**Accuracy and consistency.** Improved process control is ensured by reducing the risk of under and over tightening, due to the unique Breaking Technology

**Calibrated scale.** A visible micrometer style scale allows the user to adjust the tool quickly and easily to their desired torque setting, enabling a range of different torque settings to be applied

**Long tool life.** High quality, durable design and construction, minimises replacement and downtime costs

**Process Control.** Reduces the likelihood of warranty and rework by assuring process control through accurate and repeatable torque application

**Production efficiency.** Improved operator comfort and productivity, from the ergonomic design, which includes lightweight materials and moulded plastic handgrip

**Versatility.** Versatile tools ideal for Maintenance & Repair applications where a range of torques can be applied quickly and easily to a variety of fasteners and connectors

### Additional features

1/4", 3/8", 1/2" interchangeable ratchet heads come as standard

Available in N.m or lbf.in or lbf.ft versions

For details of Wrench End Fittings & Sockets. **See pages 72-74**

Tool can be kept accurate and up to date with our Calibration service. **See page 82 for details**



**For more information:** Tool Selector; [gedore-torque.com/tool-selector](http://gedore-torque.com/tool-selector) Telephone; +44 (0) 1483 894 476  
Videos; [www.youtube.com/gedore-torque](http://www.youtube.com/gedore-torque) Email; [salesandrepairs@gedore-torque.com](mailto:salesandrepairs@gedore-torque.com)

Want to know how to use this tool?

**YouTube**

Watch our video

Order Code	Model	ISO	Calibrated Range			Drive	k mm	kg	Accuracy	ISO 6789 Class
			ISO	Imperial	Imperial					
050636	ATB 25 D	5-25 N.m	0.1 N.m	-	-	1/4"	345	1.11	+/- 4%	2A
050641	ATB 25 D	-	-	50-250 lbf.in	1 lbf.in	1/4"	345	1.11	+/- 4%	2A
050646	ATB 25 D	-	-	4-20 lbf.ft	0.1 lbf.ft	1/4"	345	1.11	+/- 4%	2A
050638	ATB 25 A	5-25 N.m	0.1 N.m	-	-	3/8"	345	1.12	+/- 4%	2A
050643	ATB 25 A	-	-	50-250 lbf.in	1 lbf.in	3/8"	345	1.12	+/- 4%	2A
050648	ATB 25 A	-	-	4-20 lbf.ft	0.1 lbf.ft	3/8"	345	1.12	+/- 4%	2A
050685	ATB 50	10-50 N.m	0.25 N.m	-	-	3/8"	365	1.14	+/- 4%	2A
050690	ATB 50	-	-	120-440 lbf.in	2 lbf.in	3/8"	365	1.14	+/- 4%	2A
050695	ATB 50	-	-	7-37 lbf.ft	0.125 lbf.ft	3/8"	365	1.14	+/- 4%	2A
050735	ATB 100	20-100 N.m	0.5 N.m	-	-	1/2"	400	1.30	+/- 4%	2A
050740	ATB 100	-	-	240-880 lbf.in	4 lbf.in	1/2"	400	1.30	+/- 4%	2A
050745	ATB 100	-	-	14-74 lbf.ft	0.25 lbf.ft	1/2"	400	1.30	+/- 4%	2A