



Application Tooling > Portable Crimp Tools



Tool Grade: **Commercial Crimp Tooling**
Ratchet Configuration: **Operator Releasable & Adjustable**
Die Sets Type: **Removable/Interchangeable**
Specification Type: **TE Product Specification (114-)**
TE Certification: **Upon Request for Fee**

Features

Other

Crimp Form-Wire Barrel Type	Open Barrel - F Crimp
Tool Grade	Commercial Crimp Tooling
Ratchet Configuration	Operator Releasable & Adjustable
Die Sets Type	Removable/Interchangeable
Specification Type	TE Product Specification (114-)
TE Certification	Upon Request for Fee
Power Technology Type	Manual
Tooling Type	Ergocrimp Hand Tool Assembly or Die

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JAN 2022 (223) SVHC > Threshold: Not Yet Reviewed



Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 42565-2 FF 250 TAB 18-14AWG TPBR PRE CRIMPED	 TE Part # 6-160449-5 FF 250 REC 1.0-2.5MM2 TPBR LP	 TE Part # 5-160447-2 FF 250 REC 1.0-2.5MM2 TPPB LP	 TE Part # 6-160449-2 FF 250 REC 1.0-2.5MM2 TPPB LP
 TE Part # 6-160449-3 FF 250 REC 1-2.5MM2 PB SILVER PLATED LP	 TE Part # 5-160447-3 FF 250 REC 1-2.5MM2 PB SILVER PLATED LP	 TE Part # 5-160447-5 FF 250 REC 1.0-2.5MM2 PRBR LP	 TE Part # 5-160447-4 FF 250 REC 1.0-2.5MM2 BR LP
 TE Part # 6-160449-6 FF 250 REC 1-2.5MM2 BR SILVER PLATED LP	 TE Part # 5-160447-6 FF 250 REC 1-2.5MM2 BR SILVER PLATED LP		

Customers Also Bought



 TE Part #91505-1 CCII TYPE III+ 24-16 ASSY	 TE Part #539635-1 ERGO HAND TOOL FRAME-NO DIES	 TE Part #1452426-1 EXTRACTION TOOL	 TE Part #6-1579007-0 EXTRACTION TOOL
 TE Part #823692-000 301A034-25-0	 TE Part #6-160449-2 FF 250 REC 1.0-2.5MM2 TPPB LP	 TE Part #1-962841-1 TAB 2.8x0.8 CONTACT CS SRC Sn	 TE Part #929930-3 JUN-POW-TIM CONTACT L/P
 TE Part #170020-1 SHUR PLUG 20-14 MM2 TPBR	 TE Part #539951-2 ERGO DIE MCP 2,8K		

Documents

Product Drawings

DIE F6. 3FF

English

Datasheets & Catalog Pages

1-1773865-2_1015_Commercial Manual Hand Tools

English

Bottoming Dies

English

Instruction Sheets

Instruction Sheet (non U.S.)

German