

Product: iglidur[®] J260

19.11.2013

General Properties:

density: ³⁾	1.35 g/cm ³
colour:	yellow
saturation with moisture absorption at 23°C / 50% r. h.:	0.2 weight %
saturation with water:	0.4 weight %

Mechanical Properties: ³⁾

flexural modulus:	1000 MPa
flexural strength:	43 / 13 MPa ⁴⁾
max. permissible surface pressure at 20 °C:	24 MPa
Shore D hardness:	66

Thermal Properties:

highest long term service temperature ¹⁾ :	120°C
highest short term service temperature ^{1), 2)} :	140°C
highest short term ambient temperature ^{1), 2)} :	140°C
lowest service temperature:	-100°C

Electrical Properties: ³⁾

surface resistivity:	>10 ¹⁰ Ω
----------------------	---------------------

¹⁾ relaxation possible

²⁾ without additional load; no movement

³⁾ Depends on the printing parameters

⁴⁾ Printed flat / upright

The information on this Product Data Sheet is based on our current knowledge of the specified product. None of the information comprises one or more guarantees on certain properties .

Erstellt: 19.11.2013/Dr. Ralf Selzer/ Entwicklung

F-2-0034-A

i:\gleitlager\konstruktion\produktentwicklung\igidur\datenblätter\werkstoffdatenblätter\product data sheets iglide 2013 metric\igidur j260 3d-printed product data sheet2015.doc

Geändert:

Verteiler: Technisches Marketing, Entwicklung

Stand: A

Seite 1 von 1