




MBCK41-20-20-A

Ruland MBCK41-20-20-A, 20mm x 20mm Bellows Coupling with Keyways, High Stiffness, Aluminum, 41.3mm, OD 51.7mm Length



Description

Ruland MBCK41-20-20-A is a high stiffness bellows coupling with 20mm x 20mm bores, 41.3mm OD, 51.7mm length, and 6mm x 6mm keyways. It has fewer convolutions than comparably sized increased misalignment styles allowing for increased torsional stiffness making it the ideal choice for precision positioning applications. MBCK41-20-20-A is comprised of two anodized aluminum hubs and a stainless steel bellows for lightweight and low inertia. It is also engineered with a balanced design for reduced vibration at high speeds up to 10,000 RPM. The thin walls of the bellows are able to flex while remaining rigid under torsional loads allowing for the accommodation of all forms of misalignment. Hardware is metric and tests beyond DIN 912 12.9 standards for maximum torque capabilities. MBCK41-20-20-A is machined from meticulously selected bar stock that is sourced exclusively from North American mills. It is carefully made in our ISO 9001:2015 advanced manufacturing facility in Marlborough, MA under strict controls using proprietary processes. MBCK41-20-20-A is RoHS3, REACH, and Conflict Minerals compliant.

Product Specifications

Bore (B1)	20 mm	Small Bore (B2)	20 mm
Keyway (K1)	6 mm	Keyway (K2)	6 mm
B1 Max Shaft Penetration	24.0 mm	B2 Max Shaft Penetration	24.0 mm
Outer Diameter (OD)	1.625 in (41.3 mm)	Bore Tolerance	+0.03 mm / -0.00 mm
Length (L)	2.035 in (51.7 mm)	Length Tolerance	+/- 0.76 mm
Hub Width (LH)	18.05 mm	Recommended Shaft Tolerance	+0.000 mm / -0.013 mm
Key Width (K1)	6 mm	Key Width (K2)	6 mm
Key Height (K1)	6 mm	Key Height (K2)	6 mm
Keyway 1 Height (T1)	22.8 mm	Keyway 2 Height (T2)	22.8 mm
Keyway 1 Width Tolerance	+0.015 mm / -0.015 mm	Keyway 1 Height Tolerance	+0.1 mm / 0 mm
Keyway 2 Width Tolerance	+0.015 mm / -0.015 mm	Keyway 2 Height Tolerance	+0.1 mm / 0 mm
Forged Clamp Screw	M4	Screw Material	Alloy Steel
Hex Wrench Size	3.0 mm	Screw Finish	Black Oxide
Seating Torque	4.6 Nm	Number of Screws	2 ea
Dynamic Torque Reversing	7.00 Nm	Angular Misalignment	2.0°
Dynamic Torque Non-Reversing	14.00 Nm	Parallel Misalignment	0.25 mm
Static Torque	28.0 Nm	Axial Motion	0.50 mm
Torsional Stiffness	63 Nm/Deg	Moment of Inertia	2.957 x 10 ⁻⁵ kg-m ²
Maximum Speed	10,000 RPM	Full Bearing Support Required?	Yes
Average Load at Max Parallel Offset	85.27 N	Average Slope	334 N/mm
Zero-Backlash?	Yes	Balanced Design	Yes
Torque Wrench	TW:BT-1R-1/4-41.0	Recommended Hex Key	Metric Hex Keys
Material Specification	Hubs: 2024-T351 Aluminum Bar Bellows: Type 321 Stainless Steel	Temperature	-40°F to 200°F (-40°C to 93°C)
Finish Specification	Sulfuric Anodized MIL-A-8625 Type II, Class 2 and ASTM B580 Type B	Bellows Attachment Method	Epoxy

Black Anodize

Manufacturer	Ruland Manufacturing	Country of Origin	USA
Weight (lbs)	0.248400	UPC	634529166758
Tariff Code	8483.60.8000	UNSPC	31163018
Note 1	Stainless steel hubs are available upon request.		
Note 2	Torque ratings are at maximum misalignment.		
Note 3	Performance ratings are for guidance only. The user must determine suitability for a particular application.		
Note 4	Torque ratings for the couplings are based on the physical limitations/failure point of the metal bellows. Under normal/typical conditions the hubs are capable of holding up to the rated torque of the metal bellows. Please consult technical support for more assistance.		

Prop 65

WARNING This product can expose you to chemicals including Ethylene Thiourea and Nickel (metallic), known to the State of California to cause cancer, and Bisphenol A and Ethylene Thiourea, known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov.

Installation Instructions

1. Align the bores of the MBCK41-20-20-A bellows coupling on the shafts that are to be joined and determine if the misalignment parameters are within the limits of the coupling. (*Angular Misalignment: 2.0°, Parallel Misalignment: 0.25 mm, Axial Motion: 0.50 mm*)
2. Fully tighten the M4 screw on the first hub to the recommended seating torque of 4.6 Nm using a 3.0 mm hex torque wrench.
3. Before tightening the screw on the second hub, rotate the coupling by hand to allow it to reach its free length.
4. Tighten the screw on the second hub to the recommended seating torque. Make sure the coupling remains axially relaxed and the misalignment angle remains centered along the length of the coupling.
5. The shafts may extend into the relieved portion of the bore as long as it does not exceed the shaft penetration length of 24.0 mm.