

Unrivalled combination of chemical resistance, confident grip and a comfortable inner lining.



- The AlphaTec® glove incorporates revolutionary Ansell Grip Technology™ to enable users to handle wet or oily objects with less grip force and more control. This unique combination of liquid-proof chemical resistance and grip, together with flexibility and dexterity, makes the AlphaTec® glove the logical choice when working with chemicals.
- Reliable chemical protection for added user safety. The patented Ansell Grip Technology™ ensures that the coating polymer does not penetrate the liner during manufacture. The coating is therefore consistent and sound, significantly reducing the likelihood of chemical leakage onto the skin.
- AlphaTec® models with white nylon liner are recommended for indoor applications

Industries

- Automotive
- Automotive Aftermarket
- Machinery and Equipment
- Metal fabrication
- Chemical
- Oil and gas

Applications

- Metalworking & assembly operations
- Body painting including surface inspection
- Applying sealers, touching up
- Changing tools and dies
- Handling application & cleaning tools
- Warehousing of raw materials
- Loading and unloading trucks and vehicles
- Filling, blending and charging of raw materials
- Transferring liquids and solids
- Loading and unloading of process equipment
- Transferring liquids and solids between vessels and tanks and process equipment
- Supervision of running operation
- Handling outgoing goods: cans, vessels, bulkpack and cartons
- Opening furnaces draining pumps valves or lines and crackers BTX process

Key Features

- Featuring ANSELL GRIP™ technology to enable users to handle wet or oily objects with better grip and more control
- Solid nitrile shell for high protection against exposure to bases, oils, fuels, some solvents and greases
- Utilizes white nylon liner which is ideal for indoor applications
- Vend pack option available

Vulcanization Chemical Accelerators

- Zinc Diethyldithiocarbamate

Only a very small number of users may be sensitive to this ingredient(s) and hence may develop irritant and/or allergic contact reactions.

Technologies



Performance Standards



Specifications

BRAND STYLE	DESCRIPTION	SIZE	LENGTH	COLOR	PACKAGE
AlphaTec® 58-530W	Nylon, Nitrile, Ansell Grip™	7, 8, 9, 10, 11	290-316 mm / 11-12 inches	Grey	<ul style="list-style-type: none"> • 6 pairs/polybag; 12 polybags/carton • Vend pack variant ,1 pair per bag,72 bags per carton

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 210
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

Canada

Ansell Canada Inc.
105, rue Lauder
Cowansville (Québec)
J2K 2K8, Canada
T: 1 800 363-8340
F: 1 888 267-3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2021 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.