

R46_275_MIN, Film, Metallized Polypropylene, Safety, 2.2 uF, 20%, 275 VAC (X2), 560 VDC, 110°C, Lead Spacing = 22.5mm



Dimensions

L	26.5mm +0.3mm
H	22mm +0.1mm
T	13mm +0.2mm
S	22.5mm +/-0.4mm
LL	4mm +2mm
F	0.8mm +/-0.05mm

Packaging Specifications

Packaging:	Bulk, Bag
Packaging Quantity:	300

General Information

Supplier:	KEMET
Series:	R46_275_MIN
Dielectric:	Metallized Polypropylene
Style:	Radial
Features:	EMI Safety
RoHS:	Yes
Lead:	Cut
Qualifications:	ENEC, UL, cUL, CQC

Specifications

Capacitance:	2.2 uF
Capacitance Tolerance:	20%
Voltage AC:	275 VAC (X2)
Voltage DC:	560 VDC
Temperature Range:	-40/+110C
Rated Temperature:	110°C
Dissipation Factor:	0.10% 1kHz
Insulation Resistance:	13.6364 GOhms
Max dV/dt:	200 V/us
Safety Class:	X2