



All GET .64 CONNECTOR SYSTEM, CONNECTOR HSG (62)

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) SVHC > Threshold: Dodecamethylcyclohexasiloxane (D6) (.5% in 27519454045) Decamethylcyclopentasiloxane (D5) (.5% in 27519454045) Octamethylcyclotetrasiloxane (D4) (.5% in 27519454045) <b>Article Safe Usage Statements:</b> Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products



will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1488572-1  
50 WAY 45 DEGREE EXIT WIRE DRE




TE Part # CAT-G3353-T273  
GET .64 CONNECTOR SYSTEM,  
RECEPT AND TAB




TE Part # 1438126-1  
50 WAY WIRE SHIELD (PROD)


Customers Also Bought




TE Part #2293333-1  
16POS,GEN 50,REC HSG,ASSY




TE Part #2035360-1  
1X4 GENERATION Y ASSY KEY A




TE Part #2098634-1  
Carrier, 20P, GY LAC, Black




TE Part #2098634-2  
Carrier, 20P, GY LAC, Black




TE Part #2351963-2  
46POS,HYBRID,REC HSG ASSY,SLD,  
COD A




TE Part #1924639-1  
1X8 FEMALE ASSY KEY C, LP LATC




TE Part #2386232-1  
REC CONN CVR ASSY,46POS,0.64  
GENER. Y



TE Part #2377194-1  
CVTY PLUG,0.64 GENER. Y,CVTY DIA,  
MAT-SL



TE Part #1-1326031-0  
2.8MM BLD,SEAL,14AWG,REV REEL



TE Part #2098216-1  
32P Carrier, GY

Documents

Product Drawings



50 WAY HARNESS ASSY KEYB(PROD)

English

CAD Files

Customer View Model

ENG\_CVM\_CVM\_1438129-2\_AL1.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_1438129-2\_AL1.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_1438129-2\_AL1.3d\_stp.zip

English

3D PDF

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

GET 0.64 Interconnection System

English

Instruction Sheets

Instruction Sheet (U.S.)

English