



AMPLIMITE | AMPLIMITE HD-20


TE Internal #: 747871-2

TE Internal Description: 09 PLUG SP/FMS STD

D-Sub Plug Assembly: Standard, Vertical, Shell Size 1, 2.74mm

[View on TE.com >](#)

Connectors > D-Shaped Connectors > D-Sub Plug Assembly: Standard, Vertical, Shell Size 1, 2.74mm



Number of Positions: 9

Connector & Housing Type: Plug

Connector System: Board-to-Board

Connector Mounting Type: Board Mount

Connector Shell Size: 1

[All D-Sub Plug Assembly: Standard, Vertical, Shell Size 1, 2.74mm \(28\)](#)

Features

Product Type Features

Ground Feature Type	Grounding Indents
Shell Material Configuration	Front Metal Shell
Connector & Housing Type	Plug
Connector System	Board-to-Board
Connector Shell Size	1
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Number of Positions	9
Number of Rows	2
PCB Mount Orientation	Vertical

Body Features

Shell Plating Material	Tin
Primary Product Color	Black

Connector Profile	Standard
-------------------	----------

Contact Features

	30 µin
Contact Underplating Material	Palladium Nickel
Contact Mating Area Plating Material	Gold (Au)
Contact Base Material	Brass
PCB Contact Termination Area Plating Material	Tin-Lead
Contact Shape & Form	Round
Contact Current Rating (Max)	6 A
Contact Options	Installed

Termination Features

Termination Post & Tail Diameter	.66 mm[.026 in]
Termination Method to PCB	Through Hole - Solder
Termination Post & Tail Length	3.18 mm[.125 in]

Mechanical Attachment

Mounting Hole Diameter	3.05 mm[.12 in]
Connector Mounting Type	Board Mount
PCB Mount Retention	With
PCB Mount Retention Type	Mounting Hole
Mating Retention	Without

Housing Features

Housing Material	Thermoplastic
Shell Material	Carbon Steel
Centerline (Pitch)	2.74 mm[.108 in]

Dimensions

PCB Thickness (Recommended)	1.57 – 2.36 mm[.062 – .093 in]
Row-to-Row Spacing	2.84 mm[.112 in]

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Signal
---------------------	--------

Industry Standards

UL Flammability Rating	UL 94V-0
Compatible With Approved Standards Products	UL E28476

Packaging Features

Packaging Quantity	17
Packaging Method	Tube

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2024 (241) SVHC > Threshold: Pb (13% in Component Part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not lead free process capable

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-AM7-253
IDC D-Sub: Receptacle Assembly, Low Profile, Signal, 2.77 mm



TE Part # CAT-AM7-248H8
IDC D-Sub: Receptacle Assembly, Wire to Wire, Signal, 2.74 mm




TE Part # 747516-7
09 HDE PMOLD RCPT, LEAD FREE



TE Part # 1-747943-5
KIT,RCPT,9P,HDE,SHLD ENCLSR

Also in the Series | AMPLIMITE HD-20



D-Shaped Connectors(285)



PCB D-Sub Connectors(285)


Customers Also Bought




TE Part #5-102589-4
30 MODII 2PC HDR DRRA SHRD, ROHS




TE Part #CAT-018-DRARA127
D-Sub Receptacle Assembly: Right Angle, 1.27mm



TE Part #2-1410271-1
MULTI-GIG PWR .8" R/A HDR 4P LEAD-FREE



TE Part #2101423-1
A600R,Sz3,Q11/Q11/blk/Q11/Q11/85



TE Part #2363704-2
MBXLE R/A HEADER 12S+2P



TE Part #6450571-2
MBXL R/A RCPT 24S+8P



TE Part #6450881-4
MBXLE R/A RCPT 16S+2P



TE Part #1-6450881-4
MBXLE R/A REC 12S+2P



TE Part #2343566-1
CAGE ASSY, 1X4, QSFP28, SPRING, HS



Documents

Product Drawings

09 PLUG SP/FMS STD

English

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_747871-2_P.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_747871-2_P.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_747871-2_P.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English