


ESH, Aluminum Electrolytic, 2,200 uF, 20%, 50 VDC, -40/+105°C, Lead Spacing = 7.5mm

**Dimensions**

D	18mm +/-0.5mm
L	36mm +2mm
S	7.5mm +/-0.5mm
LL Negative	15mm MIN
LL Positive	20mm MIN
F	0.8mm NOM

Packaging Specifications

Packaging:	Bulk, Bag
Packaging Quantity:	500

General Information

Supplier:	KEMET
Series:	ESH
Dielectric:	Aluminum Electrolytic
Description:	High CV Single Ended Aluminum Electrolytic
Features:	High CV
RoHS:	Yes
Lead:	Wire Leads
AEC-Q200:	No

Specifications

Capacitance:	2,200 uF
Capacitance Tolerance:	20%
Voltage DC:	50 VDC, 63 VDC (Surge)
Temperature Range:	-40/+105°C
Rated Temperature:	105°C
Life:	2000 Hrs
Dissipation Factor:	12.00%
Ripple Current:	1530 mAmps (120Hz 105C)
Leakage Current:	1100 uA (2min 20°C)
Impedance Ratio at -25C:	2
Impedance Ratio at -40C:	3