



Terminal blocks spring connection

Standard

 DIN 3




End stop	th. 9,0 mm	BADL V0	0199 408.02
Other end stops: See Accessories section			
Rail	35 x 7,5 x 1	PR3Z2	0174 300.17
Rail	35 x 15 x 2,3	PR4	0168 500.12
Rail	35 x 15 x 1,5	PR5	0168 700.22
Other rails: See Accessories section			
Other accessories: See Accessories section			


Notes

The use of some accessories may decrease the block's voltage rating. For more information, consult us.

One wire per spring.
Terminal block body material is UL 94 V0.

Accessories

	1 End section	grey	FED6.4L	V0	th. 2,5 mm	0291 696.26
		orange	FED6.4L	V0	th. 2,5 mm	0291 697.27
	2 Separator	orange			th.	
	3 Test plug	black	FC2	V2	DIA. 2 mm	0007 865.26
	4 Jumper bar	orange	BJDL6.2	V0	2 poles	0291 128.24
			BJDL6.3	V0	3 poles	0291 129.25
			BJDL6.4	V0	4 poles	0291 194.17
			BJDL6.5	V0	5 poles	0291 195.10
	Jumper bar	orange				
	IP 20 - 41 A					
	5 Jumper bar	orange	BJDPL56	(1)		0291 150.06
	For blocks of different spacing					
	- Spacing 5 and 6 mm IP 20 - 24 A					
	- Spacing 5 and 8 mm IP 20 - 24 A					
	- Spacing 5 and 10 mm IP 20 - 24 A					
	- Spacing 6 and 8 mm IP 20 - 32 A					
	- Spacing 6 and 10 mm IP 20 - 32 A					
	- Spacing 8 and 10 mm IP 20 - 41 A					




R



R See section on markers marking method

D 4/6.4L


Spacing 6 mm +0,05 .238"



4 springs.




D 6/8.2L




Spacing 8 mm -0,05 .315"



2 springs.



Color	Type	Part number
Grey	 D 4/6.4L	0290 410.06
Orange	 D 4/6.4L	0290 411.23
Blue	 D 4/6.N.4L	0290 412.24

Color	Type	Part number
Grey	 D 6/8.2L	0290 081.24
Orange	 D 6/8.2L	0290 082.25
Blue	 D 6/8.N.2L	0290 083.26

Characteristics

Wire size

	IEC NFC DIN	UL	CSA
Solid wire	0,2-6 mm ²	24-10 AWG	24-10 AWG
Stranded wire	0,2-4 mm ²	24-10 AWG	24-10 AWG
With isolated ferrule	0,5-4 mm ²		

Voltage

Rated	800 V	600 V	600 V
Pulse	8 kV		
Pollution degree	3		

Current

Rated	32 A	25 A	25 A
-------	------	------	------

Wire size

Rated / Gauge	4 mm ² / A4	10 AWG	10 AWG
Wire strip. length	Recomm. torque	Protection	
11 mm	4 mm	IP 20	
.43"	.16"	NEMA 1	

Characteristics

Wire size

	IEC NFC DIN	UL	CSA
Solid wire	0,5-10 mm ²	22-8 AWG	22-8 AWG
Stranded wire	0,5-6 mm ²	22-8 AWG	22-8 AWG
With isolated ferrule	0,5-6 mm ²		

Voltage

Rated	800 V	600 V	600 V
Pulse	8 kV		
Pollution degree	3		

Current

Rated	41 A	40 A	40 A
-------	------	------	------

Wire size

Rated/gauge	6 mm ² / A5	8 AWG	8 AWG
Wire strip. length	Recomm. torque	Protection	
12,5 mm	5,5 mm	IP 20	
.49"	.22"	NEMA 1	

Type	Part number
FED6.4L V0 th. 2,5 mm	0291 696.26
FED6.4L V0 th. 2,5 mm	0291 697.27
FC2 V2 DIA. 2 mm	0007 865.26
BJDL6.2 V0 2 poles	0291 128.24
BJDL6.3 V0 3 poles	0291 129.25
BJDL6.4 V0 4 poles	0291 194.17
BJDL6.5 V0 5 poles	0291 195.10
BJDPL56 (1)	0291 150.06
BJDPL68 (1)	0291 170.02
BJDPL610 (1)	0291 482.10

Type	Part number
FED8.2L V0 th. 2,5 mm	0291 161.25
FED8.2L V0 th. 2,5 mm	0291 162.26
FC2 V2 DIA. 2 mm	0007 865.26
BJDL8.2 V0 2 poles	0291 122.16
BJDL8.3 V0 3 poles	0291 123.17
BJDL8.4 V0 4 poles	0291 144.24
BJDL8.5 V0 5 poles	0291 145.25
BJDPL58 (1)	0291 160.00
BJDPL68 (1)	0291 170.02
BJDPL810 (1)	0291 484.12

On top : RC 610 (6) or RPC (20)
On sides : RC 65 (5)

On top : RC 610 (6) or RC 810 (17) or RPC (20)
On sides : RC 65 (5) or RCAL85 (25)

(1) End section must be inserted between 2 interconnected blocks.