


# Cam followers



Dimensions				Basic load ratings		Fatigue load limit	Maximum radial loads		Limiting speed	Mass	Designation
D	d	B	C	dynamic C	static C <sub>0</sub>	P <sub>u</sub>	dynamic F <sub>r</sub>	static F <sub>0r</sub>	r/min	kg	-
mm				kN		kN	kN				
22	10	36	12	4,4	5	0,56	4,25	6	5300	0,043	KR 22 PPA



- Appertaining grease nipple(s)** NIP A1x4.5
- Appertaining hexagonal nut**
  - Size, mm M 10x1
  - Rec. tightening torque, Nm 15
- Internal hexagon in stud**
  - Key width, mm 5