

TDG M60000

- **Part number : TDG M60000**
- **Description : Precision axial grinder**
- **Clamps : D 3 mm**
- **Air consumption : 30 l/min. (unloaded)**
- **Rotation speed : 60 000 rpm**
- **Inlet thread : 1/4" BSPF**
- **Hose ID : 10 mm (3/8")**
- **Working pressure : 6,3 bar**
- **Sound level : 95 dBa**
- **Vibrations : 2,4 m/s²**
- **Lenght : 132 mm**
- **Weight : 0,3 kg**
- **Material : Aluminium**



Applications

