



Connectors > Connector Accessories > Connector Strain Relief



Strain Relief Accessory Type: **Strain Relief Adapter**

Primary Product Material: **Nylon**

Primary Product Color: **White**

UL Flammability Rating: **UL 94V-0**

Features

Product Type Features

Strain Relief Accessory Type	Strain Relief Adapter
------------------------------	-----------------------

Body Features

Primary Product Material	Nylon
Primary Product Color	White

Industry Standards

Compatible With Agency/Standards Products	UL
UL Flammability Rating	UL 94V-0

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247)



Candidate List Declared Against: JAN 2025
(247)

Does not contain REACH SVHC

Halogen Content

Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability

Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # 641778-1
UMNL STR/REL ADAPTER



TE Part # 350848-5
05P UMNL PLUG TEST ASSY 94V0



TE Part # 641777-2
UMNL STR/REL ADAPTER *NO NIBS*




TE Part # 643182-1
UMNL STR/REL ADAPTER CAP NATL



TE Part # 641778-2
UMNL STR/REL ADAPTER *NO NIBS*



TE Part # 641777-1
UMNL STR/REL ADAPTER NATL



TE Part # 643182-2
UMNL STR/REL ADAPTER CAP


Also in the Series | [Universal MATE-N-LOK](#)



Circular Power Connectors(2)



Connector Caps & Covers(34)



Connector Hardware(12)




Connector Seals & Cavity Plugs(27)



Connector Strain Relief(7)




Insertion & Extraction Tools(4)



PCB Headers & Receptacles(285)




Rectangular Power Connectors(643)




Wire-to-Board Headers & Receptacles (285)


Customers Also Bought



TE Part #758771-000
FLDWC0311-16-2



TE Part #008805-000
FLDWC0311-16-6



TE Part #4-1601090-2
031-161-002=TAB,2.0X.51,STDSMZ



TE Part #4-2307345-2
STD RANGE WIRE TO TAB,080X020, SMZ



TE Part #EQ08983001
FLDWC0311-24-2CK1500



TE Part #EQ08993001
FLDWC0311-24-9CK1500



TE Part #EQ08973001
FLDWC0311-24-0CK1500



TE Part #5-240693-8
ANVIL



Documents

Product Drawings

[UMNL STR/REL ADAPTER CAP](#)

English

CAD Files

Customer View Model

[ENG_CVM_643131-2_D.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_643131-2_D.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_643131-2_D.2d_dxf.zip](#)

English

[3D PDF](#)

English

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_643131-2_N.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_643131-2_N.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_643131-2_N.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Application Specification](#)

English