

Description

STAINLESS STEEL TOP PLATE CASTOR, RED POLYURETHANE 100MM

Fixed

KF41BA100-28L



Part Number

Swivel

KP41BA100-28L




Swivel and brake

KP41BD100-28L



	Fixed	Swivel	Swivel+brake
Wheel Diameter ØD	100 mm		
Overall Height H	128 mm ±1		
Size of plate A X B	105 x 85 mm±1		
Plate hole centres a x b	80 x 60 mm±0,3		
Plate hole	9 mm		
Offset F ±1	\	36 mm	36 mm
Width of Tread	30 mm±0,5		
Hardness of tread	shore A ± 98		
Load capacity	150 Kg		
Weight	0,53 kg	0,7 kg	0,9 kg
Temperature	- 20 / + 60 °C		



Castor Assembly :

Pressed stainless steel -AISI 304-. Swivel on two rows of balls.
Fastening by top plate.
Total lock. Metal pedal.

Wheel :

Wheel centre made of White Polyamide.
Tread : Red injected Polyurethane non marking.
Hub : Plain bore.

Features :

Low starting effort. High load capacity.
Lightweight, highly resistant to knocks and other impacts, abrasion as well as a great many chemical substances.
Corrosion resistant, easy to clean. Specially designed for humid environments.
Suited for Food industry, Hospital or Industrial Kitchen equipment.
Non staining red tyre.
Medium duty.