



Connectors > Connector Accessories > Connector Hardware



Connector Hardware Accessory Type: **Guide Socket Module**

Primary Product Material: **Stainless Steel**

Operating Temperature (Max): **125 °C [257 °F]**

Operating Temperature Range: **-55 – 125 °C [-67 – 257 °F]**

Hardware Accessory Function: **Guide Hardware**

Features

Product Type Features

Connector Hardware Accessory Type	Guide Socket Module
Hardware Accessory Function	Guide Hardware

Configuration Features

Key Orientation	315°
Accessory Placement Location	Front Board

Body Features

Primary Product Plating Material	Nickel
Product Orientation	Right Angle
Primary Product Material	Stainless Steel

Mechanical Attachment

Product Plating Finish	Passivated
Product Mount Type	Board Mount

Usage Conditions

Operating Temperature (Max)	125 °C[257 °F]
Operating Temperature Range	-55 – 125 °C[-67 – 257 °F]



Industry Standards

Industry Standard	VITA 46
-------------------	---------

Packaging Features

Packaging Method	Bag
Packaging Quantity	1

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 2000676-2
Keyed Guide Pin, Machined, Vita 46

Customers Also Bought



TE Part #1-2000676-2
KEYED GUIDE PIN, MACHINED,
MULTIGIG, 19MM



TE Part #2000713-7
RA Keyed Guide Mod, Vita 46,
Machined



TE Part #2828384-1
CONN KIT, VITA66.4-DERIV, PLUG,
DUAL-CAVITY



TE Part #2292096-1
RCPT ASSY SMT VERT 50 POSN MBC



TE Part #2000713-8
RA Keyed Guide Mod, Vita 46,
Machined




TE Part #2000713-9
RA Keyed Guide Mod, Vita 46,
Machined




TE Part #1-2000713-0
RA Keyed Guide Mod, Vita 46,
Machined



TE Part #2821750-1
SLIVER C/A, 50P, STR TO STR 25GHZ
100OHM



TE Part #256880-000
242W042-100-0



TE Part #1221286-1
SSMT-OSMT TL ENGAGE-
DISENGAGE

Documents

Product Drawings

RA Keyed Guide Mod, Vita 46, Machined

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-2000713-3_E.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_1-2000713-3_E.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-2000713-3_E.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[SOSA Aligned Interconnect Solutions](#)

English

[MULTIGIG RT 2-R Ruggedized Connectors](#)

English

Product Specifications

[Application Specification](#)

English