

# Eaton 222581

Catalog Number: 222581

Eaton Moeller® series T0 Step switches, T0, 20 A, surface mounting, 1 contact unit(s), Contacts: 2, 45 °, maintained, With 0 (Off) position, 0-3, Design number 8330

## General specifications

Product Name	Catalog Number
Eaton Moeller® series T0 Step switch	222581
EAN	Product Length/Depth
4015082225810	137 mm
Product Height	Product Width
102 mm	80 mm
Product Weight	Certifications
0.253 kg	IEC 60947
	EN 60947
	EN 60204
	VDE
	IEC/EN 60204
	VDE 0660
	IEC/EN 60947-3
	IEC/EN 60947

## Catalog Notes

Rated Short-time Withstand Current  
(Icw) for a time of 1 second

## Product specifications

### Type

Step switch

### Accessories

Black thumb grip and front plate

### Amperage Rating

20A

### Product Category

Control switches

### Voltage rating

690 V

### Features

Complete device in housing

### Actuator function

Maintained

With 0 (Off) position

### 10.10 Temperature rise

The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.

### 10.11 Short-circuit rating

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

### 10.12 Electromagnetic compatibility

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

### 10.13 Mechanical function

The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

### 10.2.2 Corrosion resistance

Meets the product standard's requirements.

### 10.2.3.1 Verification of thermal stability of enclosures

Meets the product standard's requirements.

### 10.2.3.2 Verification of resistance of insulating materials to normal heat

Meets the product standard's requirements.

### 10.2.3.3 Resist. of insul. mat. to abnormal heat/fire by internal elect. effects

Meets the product standard's requirements.

## Resources

### Brochures

Brochure - T Rotary Cam switch and P Switch-disconnector

### Catalogs

P Switch-disconnectors and T Rotary cam switches catalogue  
CA042001EN

### Declarations of conformity

DA-DC-00004927.pdf

DA-DC-00004895.pdf

### Drawings

eaton-rotary-switches-t0-changeover-switch-dimensions.eps

eaton-rotary-switches-dimensions-t0-step-switch-dimensions.eps

eaton-general-totally-insulated-t0-main-switch-symbol.eps

eaton-general-rotary-switch-t0-step-switch-symbol.eps

eaton-rotary-switches-front-plate-t0-step-switch-symbol-009.eps

### eCAD model

DA-CE-ETN.T0-1-8330\_I1

### Installation instructions

IL03801007Z2021\_06.pdf

### Installation videos

Eaton's P Switch-disconnectors used in a factory

### mCAD model

DA-CS-bauform2

DA-CD-bauform2

### Product notifications

MZ008005ZU\_Orderform\_Customized\_Switch.pdf

MZ008006ZU\_Orderform\_Customized\_Switch.pdf

### Wiring diagrams

eaton-rotary-switches-t0-step-switch-wiring-diagram-216.eps

eaton-rotary-switches-t0-step-switch-wiring-diagram-215.eps

#### 10.2.4 Resistance to ultra-violet (UV) radiation

UV resistance only in connection with protective shield.

#### 10.2.5 Lifting

Does not apply, since the entire switchgear needs to be evaluated.

#### 10.2.6 Mechanical impact

Does not apply, since the entire switchgear needs to be evaluated.

#### 10.2.7 Inscriptions

Meets the product standard's requirements.

#### 10.3 Degree of protection of assemblies

Does not apply, since the entire switchgear needs to be evaluated.

#### 10.4 Clearances and creepage distances

Meets the product standard's requirements.

#### 10.5 Protection against electric shock

Does not apply, since the entire switchgear needs to be evaluated.

#### 10.6 Incorporation of switching devices and components

Does not apply, since the entire switchgear needs to be evaluated.

#### 10.7 Internal electrical circuits and connections

Is the panel builder's responsibility.

#### 10.8 Connections for external conductors

Is the panel builder's responsibility.

#### 10.9.2 Power-frequency electric strength

Is the panel builder's responsibility.

#### 10.9.3 Impulse withstand voltage

Is the panel builder's responsibility.

#### 10.9.4 Testing of enclosures made of insulating material

Is the panel builder's responsibility.

#### Fitted with:

0 (off) position

Black thumb grip and front plate

#### Operating frequency

1200 Operations/h

#### Pollution degree

#### Climatic proofing

Damp heat, constant, to IEC 60068-2-78

Damp heat, cyclic, to IEC 60068-2-30

#### Enclosure material

Plastic

#### Rated impulse withstand voltage (Uimp)

6000 V AC

#### Actuator type

Short thumb-grip

#### Ambient operating temperature - max

40 °C

#### Ambient operating temperature - min

-25 °C

#### Ambient operating temperature (enclosed) - max

40 °C

#### Ambient operating temperature (enclosed) - min

-25 °C

#### Equipment heat dissipation, current-dependent Pvid

0 W

#### Heat dissipation capacity Pdis

0 W

#### Heat dissipation per pole, current-dependent Pvid

0.6 W

#### Number of auxiliary contacts (change-over contacts)

0

#### Number of auxiliary contacts (normally closed contacts)

0

#### Number of auxiliary contacts (normally open contacts)

0

#### Number of contact units

1

#### Rated short-time withstand current (Icw)

320 A, Contacts, 1 second

#### Electrical connection type of main circuit

Screw connection

#### Mounting position

As required

#### Rated conditional short-circuit current (I<sub>q</sub>)

6 kA

#### Mounting method

Surface

Surface mounting

#### Overvoltage category

III

#### Control circuit reliability

1 failure per 100,000 switching operations statistically determined, at 24 V DC, 10 mA)

#### Number of poles

1

#### Degree of protection

IP65

#### Number of contacts

2

#### Model

Reverser

#### Degree of protection (front side)

IP65

NEMA 12

#### Inscription

0-3

#### Lifespan, mechanical

400,000 Operations

#### Safe isolation

440 V AC, Between the contacts, According to EN 61140

#### Rated operational current (I<sub>e</sub>)

8.5 A at AC-3, 690 V star-delta

20 A at AC-3, 400 V star-delta

20 A at AC-3, 230 V star-delta

15.6 A at AC-3, 500 V star-delta

#### Screw size

M3.5, Terminal screw

#### Shock resistance

15 g, Mechanical, According to IEC/EN 60068-2-27, Half-sinusoidal shock 20 ms

#### Load rating

1.6 x I<sub>e</sub> (with intermittent operation class 12, 40 % duty

factor)

$2 \times I_e$  (with intermittent operation class 12, 25 % duty factor)

$1.3 \times I_e$  (with intermittent operation class 12, 60 % duty factor)

Tightening torque

1 Nm, Screw terminals

Number of contacts in series at DC-21A, 240 V

1

Number of contacts in series at DC-23A, 120 V

3

Number of contacts in series at DC-23A, 24 V

1

Number of contacts in series at DC-23A, 240 V

5

Number of contacts in series at DC-23A, 48 V

2

Number of contacts in series at DC-23A, 60 V

3

Rated breaking capacity at 220/230 V (cos phi to IEC 60947-3)

100 A

Rated breaking capacity at 400/415 V (cos phi to IEC 60947-3)

110 A

Rated breaking capacity at 500 V (cos phi to IEC 60947-3)

80 A

Rated breaking capacity at 660/690 V (cos phi to IEC 60947-3)

60 A

Rated making capacity up to 690 V (cos phi to IEC/EN 60947-3)

130 A

Rated operational current ( $I_e$ ) at AC-21, 440 V

20 A

Rated operational current ( $I_e$ ) at AC-23A, 230 V

13.3 A

Rated operational current ( $I_e$ ) at AC-23A, 400 V, 415 V

13.3 A

Rated operational current ( $I_e$ ) at AC-23A, 500 V

13.3 A

Rated operational current ( $I_e$ ) at AC-23A, 690 V

7.6 A

Rated operational current (I<sub>e</sub>) at AC-3, 220 V, 230 V, 240 V

11.5 A

Rated operational current (I<sub>e</sub>) at AC-3, 380 V, 400 V, 415 V

11.5 A

Rated operational current (I<sub>e</sub>) at AC-3, 500 V

9 A

Rated operational current (I<sub>e</sub>) at AC-3, 660 V, 690 V

4.9 A

Safety parameter (EN ISO 13849-1)

B10d values as per EN ISO 13849-1, table C.1

Short-circuit protection rating

20 A gG/gL, Fuse, Contacts

Terminal capacity (flexible with ferrule)

1 x (0.75 - 2.5) mm<sup>2</sup>, ferrules to DIN 46228

2 x (0.75 - 2.5) mm<sup>2</sup>, ferrules to DIN 46228

Suitable for

Ground mounting

Rated operational current (I<sub>e</sub>) at DC-1, load-break switches I/r = 1 ms

10 A

Rated operational current (I<sub>e</sub>) at DC-13, control switches L/R = 50 ms

10 A

Rated operational current (I<sub>e</sub>) at DC-21, 240 V

1 A

Rated operational current (I<sub>e</sub>) at DC-23A, 120 V

5 A

Rated operational current (I<sub>e</sub>) at DC-23A, 24 V

10 A

Rated operational current (I<sub>e</sub>) at DC-23A, 240 V

5 A

Rated operational current (I<sub>e</sub>) at DC-23A, 48 V

10 A

Rated operational current (I<sub>e</sub>) at DC-23A, 60 V

10 A

Rated operational current for specified heat dissipation (I<sub>n</sub>)

20 A

Rated operational power at AC-23A, 220/230 V, 50 Hz

3 kW

Rated operational power at AC-23A, 400 V, 50 Hz

5.5 kW

Rated operational power at AC-23A, 500 V, 50 Hz

7.5 kW

Rated operational power at AC-23A, 690 V, 50 Hz

5.5 kW

Rated operational power at AC-3, 380/400 V, 50 Hz

4 kW

Rated operational power at AC-3, 415 V, 50 Hz

5.5 kW

Rated operational power at AC-3, 690 V, 50 Hz

4 kW

Rated operational power star-delta at 220/230 V, 50 Hz

5.5 kW

Rated operational power star-delta at 380/400 V, 50 Hz

7.5 kW

Rated operational power star-delta at 500 V, 50 Hz

7.5 kW

Rated operational power star-delta at 690 V, 50 Hz

5.5 kW

Rated operational voltage (U<sub>e</sub>) at AC - max

690 V

Rated uninterrupted current (I<sub>u</sub>)

20 A

Static heat dissipation, non-current-dependent P<sub>vs</sub>

0 W

Switching angle

45 °

Voltage per contact pair in series

60 V

Terminal capacity (solid/stranded)

1 x (1 - 2.5) mm<sup>2</sup>

2 x (1 - 2.5) mm<sup>2</sup>

Uninterrupted current

Rated uninterrupted current I<sub>u</sub> is specified for max. cross-section.





Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.  
All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)