

# SACC-DSI-M8FS-8CON-M10-L180 - Device connector rear mounting



1424237

<https://www.phoenixcontact.com/gb/products/1424237>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Device connector rear mounting, 8-position, Socket, straight, M8, coding: A, Rear mounting, M10, Solder pins

## Your advantages

- Easy PCB assembly: one-piece connectors for wave soldering
- Standard pin assignments and codings for signal transmission with a uniform design-in design
- For high transmission reliability: optional shield connection to the housing and latching on the PCB

## Commercial data

|                                      |                     |
|--------------------------------------|---------------------|
| Item number                          | 1424237             |
| Packing unit                         | 20 pc               |
| Minimum order quantity               | 1 pc                |
| Sales key                            | ABQJAG              |
| Product key                          | ABQJAG              |
| Catalog page                         | Page 226 (C-2-2013) |
| GTIN                                 | 4046356712491       |
| Weight per piece (including packing) | 6.575 g             |
| Weight per piece (excluding packing) | 6.42 g              |
| Customs tariff number                | 85366990            |
| Country of origin                    | DE                  |

# SACC-DSI-M8FS-8CON-M10-L180 - Device connector rear mounting



1424237

<https://www.phoenixcontact.com/gb/products/1424237>

## Technical data

### Mounting

|               |                                 |
|---------------|---------------------------------|
| Mounting type | Rear mounting M10 With flat nut |
| Assembly note | With flat nut                   |

### Product properties

|                     |                                   |
|---------------------|-----------------------------------|
| Product type        | Circular connectors (device side) |
| Number of positions | 8                                 |
| Shielded            | no                                |
| Coding              | A                                 |
| Thread type         | M8                                |

### Insulation characteristics

|                      |    |
|----------------------|----|
| Overvoltage category | II |
| Degree of pollution  | 3  |

### Material specifications

|                                        |                              |
|----------------------------------------|------------------------------|
| Flammability rating according to UL 94 | HB                           |
| Contact material                       | CuSn                         |
| Contact surface material               | Au                           |
| Contact carrier material               | PA 6.6                       |
| Material for screw connection          | Zinc die-cast, nickel-plated |

### Electrical properties

|                       |                            |
|-----------------------|----------------------------|
| Rated surge voltage   | 0.8 kV                     |
| Contact resistance    | $\leq 3 \text{ m}\Omega$   |
| Insulation resistance | $\geq 100 \text{ M}\Omega$ |
| Nominal voltage $U_N$ | 30 V AC                    |
|                       | 30 V DC                    |
| Nominal current $I_N$ | 1.5 A                      |

### Connection data

#### Conductor connection

|                         |                                     |
|-------------------------|-------------------------------------|
| Connection method       | Solder pins                         |
| Contact connection type | Socket                              |
| Tightening torque       | 1 Nm ... 1.5 Nm (Installation-side) |

### Mechanical properties

#### Mechanical data

|                             |            |
|-----------------------------|------------|
| Insertion/withdrawal cycles | $\geq 100$ |
|-----------------------------|------------|

# SACC-DSI-M8FS-8CON-M10-L180 - Device connector rear mounting



1424237

<https://www.phoenixcontact.com/gb/products/1424237>

## Connector

### Connection 1

|                   |          |
|-------------------|----------|
| Head design       | Socket   |
| Head cable outlet | straight |
| Head thread type  | M8       |
| Coding            | A        |

## Environmental and real-life conditions

### Ambient conditions

|                                 |                  |
|---------------------------------|------------------|
| Degree of protection            | IP67             |
|                                 | IP67             |
| Ambient temperature (operation) | -40 °C ... 85 °C |

## Standards and regulations

|                          |                              |
|--------------------------|------------------------------|
| Standard designation     | M8 circular connector        |
| Standards/specifications | according to IEC 61076-2-104 |

# SACC-DSI-M8FS-8CON-M10-L180 - Device connector rear mounting




1424237

<https://www.phoenixcontact.com/gb/products/1424237>

## Drawings

Schematic diagram



Connector pin assignment of M8 socket, 8-pos., view of socket side

1424237  
<https://www.phoenixcontact.com/gb/products/1424237>

Approvals

 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/1424237>

|                                                                                                                                                      |                       |                       |                   |                             |
|------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------|-----------------------|-------------------|-----------------------------|
| <div> <b>cUL Recognized</b><br/>Approval ID: E221474-20070307</div> |                       |                       |                   |                             |
|                                                                                                                                                      | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
|                                                                                                                                                      | 30 V                  | 1.5 A                 | 26                | -                           |

|                                                                                                                                                     |                       |                       |                   |                             |
|-----------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------|-----------------------|-------------------|-----------------------------|
| <div> <b>UL Recognized</b><br/>Approval ID: E221474-20070307</div> |                       |                       |                   |                             |
|                                                                                                                                                     | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
|                                                                                                                                                     | 30 V                  | 1.5 A                 | 26                | -                           |

# SACC-DSI-M8FS-8CON-M10-L180 - Device connector rear mounting



1424237  
<https://www.phoenixcontact.com/gb/products/1424237>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27440110 |
|-------------|----------|

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC002635 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# SACC-DSI-M8FS-8CON-M10-L180 - Device connector rear mounting



1424237

<https://www.phoenixcontact.com/gb/products/1424237>

## Environmental product compliance

### EU RoHS

|                                         |      |
|-----------------------------------------|------|
| Fulfills EU RoHS substance requirements | Yes  |
| Exemption                               | 6(c) |

### China RoHS

|                                        |                                                                                                                                                                                                                                   |
|----------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-50                                                                                                                                                                                                                           |
|                                        | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

### EU REACH SVHC

|                                     |                                      |
|-------------------------------------|--------------------------------------|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1)                 |
| SCIP                                | a2f18515-48eb-45f8-9a9a-d82dfe7e033d |

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd  
Halesfield 13, Telford  
Shropshire, TF7 4PG  
01952 681700  
[info@phoenixcontact.co.uk](mailto:info@phoenixcontact.co.uk)