

6-1394461-3 x OBSOLETE

SOLARLOK

TE Internal #: 6-1394461-3

TE Internal Description: PHOTOVOLT CONN PIN NEUTRAL 2.5 sq mm

[View on TE.com >](#)



Energy & Power > Solar Connectors



Solar Connector Type: **Cable Coupler**

Solar Connector Style: **Plug**

Contact Base Material: **Copper Zinc**

Keying Type: **Neutral**

Wire Size: **14 AWG**

Features

Product Type Features

Solar Connector Type	Cable Coupler
Solar Connector Style	Plug

Configuration Features

Keying Type	Neutral
-------------	---------

Contact Features

Contact Plating Material	Silver
Contact Base Material	Copper Zinc

Housing Features

Housing Color	Black
Housing Material	Polyphenylene Oxide

Dimensions

Wire Size	2.5 mm ²
-----------	---------------------

Packaging Features

Packaging Quantity	100
--------------------	-----

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
------------------------------	---------------------------



EU ELV Directive 2000/53/EC

Compliant

China RoHS 2 Directive MIIT Order No 32, 2016

Restricted Materials Above Threshold

EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JAN 2025 (247)

Candidate List Declared Against: JUN 2018 (191)

Does not contain REACH SVHC

Halogen Content

Not Low Halogen - contains Br or Cl > 900 ppm.

Solder Process Capability

Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought



TE Part #2-1879462-8
RL73H 2B R22 1% 1K RL



TE Part #2273012-4
M8 x 1.0 Angled socket Pigtail LED




TE Part #1-1579004-2
CSV10 CRIMPING HANDTOOL
SOLARLOK 4-6



TE Part #8-1419125-5
SDT-S-106LMR,000



TE Part #2106831-1
Grounding Assy



TE Part #1-796949-8
18POS TERMINAL-BLOCK PCB MOUNT



TE Part #1-1393250-7
W28-XQAT-15=W28

Documents

[CAD Files](#)

[Customer View Model](#)



[ENG_CVM_CVM_6-1394461-3_M.2d_dxf.zip](#)

English

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_6-1394461-3_M.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_6-1394461-3_M.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[SOLARLOK_CONNECTIVITY_SYSTEMS_FOR_PV_MANUFACTURERS_3-1773458-7](#)

English

[AMERICAS_VERSION_SOLARLOK_INSTALLATION_MANUAL_2-1773458-2](#)

English

Product Specifications

[Application Specification](#)

English

Agency Approvals

[UL Report](#)

English