







Data Sheet | Item Number: 2734-1102/327-000

1-conductor female connector; lever; Push-in CAGE CLAMP®; 1.5 mm²; Pin spacing 3.5 mm; 2-pole; 100% protected against mismatching; 1,50 mm²; light gray

<https://www.wago.com/2734-1102/327-000>



Color: ■ light gray



Dimensions in mm
 $L = (\text{pole no.} \times \text{pin spacing}) + 2.4 \text{ mm}$

Female connector, 2734 Series, with 3.5 mm pin spacing

This female connector (item number 2734-1102/327-000) provides hassle-free electrical installations. Strip lengths must be between 9 and 10 mm when connecting conductors to this female connector. This product features one conductor terminal and utilizes Push-in CAGE CLAMP®. Push-in CAGE CLAMP® technology provides a universal connection solution for all conductor types. It allows both solid and fine-stranded conductors with ferrules to be inserted directly into the

clamping point without the need for tools. The item's dimensions are (9.4 x 9.95 x 24.6) mm (width x height x depth). This female connector is suitable for conductor cross sections ranging from 0.14 mm² to 1.5 mm².

The contact surface is coated with tin.

Notes	
Safety Information	The MCS – MULTI CONNECTION SYSTEM includes connectors without breaking capacity in accordance with DIN EN 61984. When used as intended, these connectors must not be connected/disconnected when live or under load. When used as intended, these connectors must not be connected/disconnected when live or under load. The circuit design should ensure header pins, which can be touched, are not live when unmated.
Variants:	Other pole numbers Other versions (or variants) can be requested from WAGO Sales or configured at https://configurator.wago.com/ .

Electrical data				
Ratings per		IEC/EN 60664-1		
Overvoltage category		III	III	II
Pollution degree		3	2	2
Nominal voltage		160 V	160 V	320 V
Rated impulse withstand voltage		2.5 kV	2.5 kV	2.5 kV
Rated current		10 A	10 A	10 A
Approvals per		UL 1059		
Use group		B	C	D
Rated voltage		300 V	-	300 V
Rated current		10 A	-	10 A
Approvals per		CSA		
Use group		B	C	D
Rated voltage		300 V	-	300 V
Rated current		10 A	-	10 A

Connection Data																						
Clamping units	2	Connection 1 <table><tr><td>Connection technology</td><td>Push-in CAGE CLAMP®</td></tr><tr><td>Actuation type</td><td>Lever</td></tr><tr><td>Solid conductor</td><td>0.14 ... 1.5 mm² / 26 ... 14 AWG</td></tr><tr><td>Solid conductor; push-in termination</td><td>0.34 ... 1.5 mm² / 22 ... 14 AWG</td></tr><tr><td>Fine-stranded conductor</td><td>0.14 ... 1.5 mm² / 26 ... 14 AWG</td></tr><tr><td>Fine-stranded conductor; with insulated ferrule</td><td>0.14 ... 0.75 mm²</td></tr><tr><td>Fine-stranded conductor; with uninsulated ferrule</td><td>0.14 ... 1 mm²</td></tr><tr><td>Strip length</td><td>9 ... 10 mm / 0.35 ... 0.39 inches</td></tr><tr><td>Pole number</td><td>2</td></tr><tr><td>Conductor entry direction to mating direction</td><td>0°</td></tr></table>	Connection technology	Push-in CAGE CLAMP®	Actuation type	Lever	Solid conductor	0.14 ... 1.5 mm² / 26 ... 14 AWG	Solid conductor; push-in termination	0.34 ... 1.5 mm² / 22 ... 14 AWG	Fine-stranded conductor	0.14 ... 1.5 mm² / 26 ... 14 AWG	Fine-stranded conductor; with insulated ferrule	0.14 ... 0.75 mm²	Fine-stranded conductor; with uninsulated ferrule	0.14 ... 1 mm²	Strip length	9 ... 10 mm / 0.35 ... 0.39 inches	Pole number	2	Conductor entry direction to mating direction	0°
Connection technology	Push-in CAGE CLAMP®																					
Actuation type	Lever																					
Solid conductor	0.14 ... 1.5 mm² / 26 ... 14 AWG																					
Solid conductor; push-in termination	0.34 ... 1.5 mm² / 22 ... 14 AWG																					
Fine-stranded conductor	0.14 ... 1.5 mm² / 26 ... 14 AWG																					
Fine-stranded conductor; with insulated ferrule	0.14 ... 0.75 mm²																					
Fine-stranded conductor; with uninsulated ferrule	0.14 ... 1 mm²																					
Strip length	9 ... 10 mm / 0.35 ... 0.39 inches																					
Pole number	2																					
Conductor entry direction to mating direction	0°																					
Total number of potentials	2																					
Number of connection types	1																					
Number of levels	1																					

Physical data

Pin spacing	3.5 mm / 0.138 inches
Width	9.4 mm / 0.37 inches
Height	9.95 mm / 0.392 inches
Depth	24.6 mm / 0.969 inches

Mechanical data

Variable coding	Yes
Anti-rotation protection	Yes

Plug-in connection

Contact type (pluggable connector)	Female connector/socket
Connector (connection type)	for conductor
Mismating protection	Yes

Material data

Note (material data)	Information on material specifications can be found here
Color	light gray
Material group	I
Insulation material (main housing)	Polyamide (PA66)
Flammability class per UL94	V0
Clamping spring material	Chrome-nickel spring steel (CrNi)
Contact material	Copper alloy
Contact Plating	Tin
Fire load	0.032 MJ
Weight	1.9 g

Environmental requirements

Limit temperature range	-60 ... +100 °C
Processing temperature	-35 ... +60 °C

Commercial data

Packaging type	Box
Country of origin	DE
GTIN	4066966215885
Customs tariff number	85366990990

Product Classification

UNSPSC	39121409
ETIM 9.0	EC002638
ETIM 10.0	EC002638
ECCN	NO US CLASSIFICATION



Environmental Product Compliance	
RoHS Compliance Status	Compliant, No Exemption

Approvals / Certificates

General approvals



Approval	Standard	Certificate Name
CSA DEKRA Certification B.V.	C22.2 No. 158	2314554
UL Underwriters Laboratories Inc.	UL 1977	E 45171
UL Underwriters Laboratories Inc.	UL 1059	UL-US-L45172-6187124-1

Downloads

Environmental Product Compliance

Compliance Search	
Environmental Product Compliance 2734-1102/327-000	↓

Documentation

Additional Information			
Technical Section	03.04.2019	pdf 2027.26 KB	↓

CAD/CAE-Data

CAD data	
2D/3D Models 2734-1102/327-000	↓

PCB Design	
Symbol and Footprint via SamacSys 2734-1102/327-000	↓
Symbol and Footprint via Ultra Librarian 2734-1102/327-000	↓



1 Compatible Products

1.1 System counterpart

1.1.1 Male connector/plug



Item No.: 734-302 1-conductor male connector; CAGE CLAMP®; 1.5 mm²; Pin spacing 3.5 mm; 2-pole; 100% protected against mismatching; light gray	Item No.: 734-162 THT male header; 1.0 x 1.0 mm solder pin; angled; 100% protected against mismatching; Pin spacing 3.5 mm; 2-pole; light gray	Item No.: 734-132 THT male header; 1.0 x 1.0 mm solder pin; straight; 100% protected against mismatching; Pin spacing 3.5 mm; 2-pole; light gray
--	--	--

1.2 Optional Accessories

1.2.1 Coding

1.2.1.1 Coding



Item No.: 2734-505 Coding pin carrier; 5 coding keys; for female connectors; orange

1.2.2 Ferrule

1.2.2.1 Ferrule



Item No.: 216-241 Ferrule; Sleeve for 0.5 mm² / 20 AWG; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90; white	Item No.: 216-141 Ferrule; Sleeve for 0.5 mm² / 20 AWG; uninsulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 1/08.92	Item No.: 216-242 Ferrule; Sleeve for 0.75 mm² / 18 AWG; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90; gray	Item No.: 216-142 Ferrule; Sleeve for 0.75 mm² / 18 AWG; uninsulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 1/08.92
--	---	--	--

1.2.3 Jumper

1.2.3.1 Jumper



Item No.: 2734-402 Jumper; for conductor entry; 2-way; insulated; light gray
--

1.2.4 Locking system

1.2.4.1 Locking system



Item No.: 2734-510 Locking lever; for female connectors; 1 part; For Push-in CAGE CLAMP® connection; lever; orange
--

1.2.5 Strain relief

1.2.5.1 Strain relief plate



Item No.: 2734-532
Strain relief plate; for female connectors; 6 mm wide; 1 part; lever; Pin spacing 3.5 mm; light gray

1.2.6 Test and measurement




1.2.6.1 Testing accessories




Item No.: 735-500
WAGO Test pin; 1 mm Ø; 30 V AC / 60 V DC; CAT0; 1 A; 6 mm uninsulated; Test lead for soldering up to 0,5mm²

Installation Notes



Conductor termination



Conductor removal



Testing



Marking

