



Example image

APPLICATION PURPOSES

- For cooling and heating water without antifreeze agent
- For cooling and heating water with antifreeze agent
- For district heating water ≤ 120 °C
- For extinguishing water (wet)
- For sprinklers (wet)
- For compressed air (oil purity class 3)
- Suitable exclusively for threads with an inner diameter of ≤ di, see table

- For technical building systems, industry and shipbuilding

CHARACTERISTICS

- Pressing indicator
- Leaky if unpressed
- Outside zinc-plated
- Union nut made of brass
- Seal ring made of CIIR, black
- Flat gasket made of EPDM

- Pressing socket with transparent protection plug

TECHNICAL DATA

Medium temperature with flat gasket EPDM	0–100 °C
Product material	Non-alloy steel 1.0034 E195 (EN 10305)

Art. no.	DN	d, ø mm	G "	di, ø mm	L cm	Z cm
25032	12	15	3/4	13	3.7	1.1
25033	15	18	3/4	13	3.7	1.1
25040	15	18	1	20	3.9	1.1
25034	20	22	1	20	4	1.1

Art. no.	DN	d, ø mm	G "	di, ø mm	L cm	Z cm
25044	20	22	1 1/4	26	4.3	1.3
25035	25	28	1 1/4	26	4.4	1.3
25050	25	28	1 1/2	32	4.6	1.3
25036	32	35	1 1/2	32	4.8	1.3
25051	32	35	2	42	4.8	1.2
25037	40	42	1 3/4	39	5.2	1.3
25052	40	42	2	42	5.4	1.4
25053	40	42	2 1/4	42	5.6	1.4
25038	50	54	2 3/8	51	5.8	1.5
25054	50	54	2 1/2	54	6.3	1.4
25055	50	54	2 3/4	57	6.3	1.4
25045	65	76.1	3	73	9.9	3.3
25046	80	88.9	3 1/2	84	11.1	3.7