



Head protection

# MILO CLEAR

## SAFETY GLASSES

Clear-lens , light and thin safety glasses



### Specific benefits



#### Comfort

- Extra flat temples for optimal comfort and less pressure
- Ultra lightweight for a better acceptance in extended period of use



#### Performance

- Excellent industrial grade protection in a contemporary angular wrap style and with wide field of vision.
- High performance optical class for less visual fatigue
- Very curved visor for the best field of view at height
- Wraparound lens provides extra wide unobstructed field of vision

### Certifications and norms



#### EN170

UV 2C - 1.2

#### EN166

1 FT / FT

#### ANSI-ISEA Z87.1 - IMPACT

Z87+ U6

### Applications

- Food & Beverage
- Maintenance
- Chemical industry
- Automotive
- Transportation
- Storage

### Protects against risks



Shock



UV / IR



Head protection

# MILO CLEAR

## SAFETY GLASSES

Clear-lens , light and thin safety glasses

### Standards - Details

### Technical details

Use	Inside
Type of eye protection	Glasses
Lens matériel	Polycarbonate
Lens treatment	Anti-scratch (classic), UV400
Lens based curve	9.5
Lens support	Monobloc
Lens color	Clear
Optical class	1
Lens protection class	1.2
Lens characteristic	Curved
Mechanical strength (lens)	F, T
Nose pad material	Polycarbonate
Frame material	Polycarbonate
Frame	Temples
Frame color	Black, Colorless
Mechanical strength (frame)	F, T
Temples benefit	Extra thin, Flexible tip
Temples confort	Flexible tip
Optional accessories	Strap, Case
Weight (g)	18








# MILO CLEAR

## SAFETY GLASSES

Clear-lens , light and thin safety glasses

Head protection

### Logistics information

Reference	Colour	Size	Designation	EAN13	Box code			Weight			
MILOIN	Clear	-	MILO CLEAR	3295249200756	13295249200753	100	10	5.148 kg	30.6 cm	39.4 cm	53.4 cm



Multiple sales



Minimum sales



Box Width



Box Depth



Box Height