

6-968974-1 ✓ ACTIVE

AMP | AMP MCP Connector System, AMP MCP 2.8


TE Internal #: 6-968974-1

18 Position Housing, Housing for Female Terminals, Wire-to-Wire, 5 mm [.197 in] Centerline, Light Blue, Wire & Cable, Power, Hybrid

[View on TE.com >](#)



Automotive Parts > Automotive Connectors > Automotive Housings > AMP Unsealed Connector Housing



Connector & Housing Type: **Housing for Female Terminals**

Number of Positions: **18**

Sealable: **No**

Operating Temperature Range: **-40 – 120 °C [ -40 – 248 °F ]**

Number of Rows: **3**

[All AMP Unsealed Connector Housing \(109\)](#)

## Features

### Product Type Features

Mixed & Hybrid Connector	No
Connector Shape	Rectangular
Connector & Housing Type	Housing for Female Terminals
Sealable	No
Primary Locking Feature	Integrated in Housing
Connector System	Wire-to-Wire
Connector & Contact Terminates To	Wire & Cable

### Configuration Features

Number of Positions	18
Number of Rows	3

### Electrical Characteristics

Operating Voltage	28 VDC
Nominal Voltage Architecture	12 V, 24 V



### Body Features

Cable Exit Angle	180°
Primary Product Color	Light Blue
Connector & Keying Code	C

### Contact Features

Contact Size	2.8mm
Contact Type	Receptacle
Mating Tab Width	2.8 mm[.11 in]

### Mechanical Attachment

Strain Relief	Without
Terminal Position Assurance	No
Mating Alignment Type	Keyed
Mating Alignment	With
Connector Mounting Type	Cable Mount (Free-Hanging)

### Housing Features

Housing Material	PBT GF
Centerline (Pitch)	5 mm[.197 in]

### Dimensions

Product Width	36 mm[1.417 in]
Row-to-Row Spacing	5.5 mm[.217 in]
Product Length	36 mm[1.417 in]
Connector Height	24 mm[.945 in]

### Usage Conditions

Operating Temperature Range	-40 – 120 °C[-40 – 248 °F]
Operating Temperature (Max)	120 °C[248 °F]

### Operation/Application

Circuit Application	Power
---------------------	-------

### Packaging Features

Packaging Method	Box
Packaging Quantity	1000

### Other

Serviceable	No
-------------	----

Connector Position Assurance Capable

No

## Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU

Compliant

EU ELV Directive 2000/53/EC

Compliant

China RoHS 2 Directive MIIT Order No 32, 2016

No Restricted Materials Above Threshold

EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JAN 2025 (247)  
Candidate List Declared Against: JAN 2025 (247)  
Does not contain REACH SVHC

Halogen Content

Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability

Not applicable for solder process capability

### Product Compliance Disclaimer





This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts







### Also in the Series | AMP MCP 2.8



### Also in the Series | AMP MCP Connector System



### Customers Also Bought



TE Part #776315-1  
68 POSITION PLUG ASSEMBLY



TE Part #CAT-T4827-CH8172  
Timer Connector Housing



TE Part #8-968974-1  
MCP2.8 GEH 18P



TE Part #4-1393306-6  
VF711F11S01/X836




TE Part #1-1718492-3  
1.5MM TAB HSG 36 POS ASSY



TE Part #1-2133346-1  
250 FASTON HSG.,REC.,1 POS,RED



TE Part #1-2133346-4  
250 FASTON HSG.,REC.,1 POS,BLACK



TE Part #368511-1  
070 MLC PLUG 20P HSG

## Documents

### Product Drawings

#### MCP2.8 HSG ASSY 18P

English

### CAD Files

#### 3D PDF

3D

#### Customer View Model

[ENG\\_CVM\\_CVM\\_6-968974-1\\_F.2d\\_dxf.zip](#)

English

#### Customer View Model

[ENG\\_CVM\\_CVM\\_6-968974-1\\_F.3d\\_igs.zip](#)

English

#### Customer View Model

[ENG\\_CVM\\_CVM\\_6-968974-1\\_F.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

### Product Specifications

#### Application Specification

English