



Satellite IoT D2D Ready

TN & NTN Dual-Mode Antenna Satellite IoT Direct to Device Ready

Direct Mount Ground Plane Independent Antenna

Covering 4G/5G/Satellite Band 25, Wi-Fi & GNSS

The L001268 direct to device (D2D) antenna family has two variants offering two 4G/5G/Satellite Band 25 cellular ports with an optional GNSS port in a compact form factor.

The cellular bands operate in dual mode, being capable of communication with both satellites and terrestrial cellular base stations. As a ground plane independent antenna, this antenna can operate on both metallic and non-metallic surfaces. This feature combined with an IP67 rating makes this antenna an ideal solution for a broad range of IoT applications in both indoor and outdoor environments.


SATELLITE IOT D2D COMMUNICATIONS

Low Earth Orbit (LEO) satellites, positioned a few hundred miles (km) above Earth, orbit rapidly and are ideal for IoT networks. A LEO satellite constellation can now support low data rate communications through specific LTE frequencies. Future upgrades are expected to support higher data rates and voice-grade services capable of calls or sending small files.

- Dual-mode capable - Supporting Terrestrial Networks (TN) and Non-Terrestrial Networks (NTN) from a single antenna
 - 698-3800 MHz terrestrial cellular coverage
 - Band 25 (1900 MHz) cellular satellite coverage
 - Testing available for other/future cellular satellite D2D frequency bands used by various network providers
- Enabling dual-mode communications via IoT devices
 - Prioritizing terrestrial networks but capable of automatically switching to satellite when the signal is weak or unavailable

REFERENCE SIGNAL RECEIVED POWER (RSRP) VALUES

The L001268-02 antenna was live-tested for receive signal strength. Data encompasses multiple satellite pass-overs, showing signal strength variation; exceeding the -120 dBm minimum for IoT devices.



An RSRP value of -120 dBm is generally the recognized minimum requirement suitable for SMS connectivity.

RSRP can be susceptible to fluctuations for a variety of reasons. These can include: satellite elevation angle; antenna radiation patterns; solar flares; atmospheric conditions, and more.

FEATURES AND BENEFITS

- Validated for use on satcom D2D networks
- Dual-Mode TN and NTN capable
- MIMO 4G/5G cellular with optional GNSS from a single antenna
- Supports CAT-M, CAT-1 to CAT-4, and NB-IoT
- Suitable for mounting on a variety of surfaces
- Radome is paintable using commonly available spray paints (must not contain metal)
- Ground plane independent, low profile, rugged and less prone to vandalizing

APPLICATIONS

- Non-Terrestrial and Terrestrial Networks
- Satellite IoT D2D (Direct to Device) applications
- IoT endpoints
- Digital display and signage
- EV charging
- Smart lockers and storage
- Ticketing systems
- Smart terminals
- Data monitoring

ELECTRICAL SPECIFICATION				
	4G/5G Cellular			
Operating Frequency (MHz)	698-760	760-960	1690-2690	3300-3800
Free Space Performance				
VSWR - Typical	<2.0:1	<1.75:1	<2.0:1	<2.0:1
Efficiency (%) Average	>40	>40	>55	>40
Peak Gain (dBi)	2.0	2.8	3.0	3.0
On Metallic Ground Plane Performance				
VSWR - Typical	<3.5:1	<2.5:1	<2.0:1	<2.0:1
Efficiency (%) Average	>40	>40	>50	>35
Peak Gain (dBi)	2.0	2.9	4.8	6.0
Isolation Between Cellular Elements (dB)	>-10			
Input Max Power (W)	20			
Polarization	Linear			
Azimuth Beamwidth	360 °, Omnidirectional			

Measured with a 3.3 ft (1 m) cable, with and without a 2 ft (0.6m) diameter ground plane

ELECTRICAL SPECIFICATION - GNSS	
Frequency (MHz)	1559-1606
Passive Antenna Gain (dBi)	3.0
LNA Gain @ Room Temperature (dB)	26 ± 3
Noise Figure @ Room Temperature (dB)	< 2.8
Max VSWR @ Room Temperature	< 2.0:1
Polarization	RHCP
Nominal Impedance (ohm)	50
Operating Supply Voltage (Vdc)	2.5-7.0
Current Consumption, Max @ room temp. (mA)	11.5 @ 3.0V
Out-of-band Signal Rejection, Min @ room temp. (dBc)	80 @ 1 – 1525 MHz 80 @ 1428 – 2700 MHz 70 @ 4900 – 5800 MHz

MECHANICAL SPECIFICATION

Dimensions - L x W x H - mm (in.)	150 x 45 x 50 (5.90 x 1.77 x 1.97)
Weight - g (oz.)	2 Port - 173 (6.10) 3 Port - 199 (7.02)
Mounting	M16 Stud
Radome	ASA (Black)
Cable	RG174 (3.3 feet / 1m)
Connector	Cellular - SMA, GNSS - SMA

ENVIRONMENTAL SPECIFICATION


Operating Temperature - °C (°F)	-40 to +85°C (-40 to +185°F)
Storage Temperature - °C (°F)	-40 to +85°C (-40 to +185°F)
Ingress Protection (IP Rating)	IP67
Material Substance Compliance	RoHS Compliant CE & UKCA Compliant

PART NUMBER	PORT COUNT	FREQUENCY COVERAGE	CONNECTOR
L001268-01	2	4G/5G Cellular x 2 - 698 - 3800 MHz	SMA Female x 2
L001268-02	3	4G/5G Cellular x 2 - 698 - 3800 MHz GNSS x 1 - 1559-1606 MHz	SMA Female x 2 SMA Female x 1

GLOBAL 4G/5G CELLULAR COVERAGE


RF BANDS	FREQUENCY
12, 13, 14, 17, 28, 29, 44, 67, 68, 85 N12, N14, N28, N29, N83	698-806 MHz
5, 6, 8, 18, 19, 20, 26, 27 N5, N8, N18, N20, N81, N82, N89, N91, N92, N93, N94	807-960 MHz
1, 2, 3, 4, 9, 10, 15, 16, 23, 25, 33, 34, 35, 36, 37, 39, 65, 66, 70 N34, N39, N65, N66, N70, N80, N84, N86, N95	1690-2200 MHz
7, 30, 38, 40, 41, 69 N30, N38, N40, N41, N90	2200-2700 MHz
22, 42, 43, 48 N48, N78	3300-3800 MHz

MECHANICAL DRAWINGS



Heat Shrink Tube Identification

	Cellular 1	Cellular 2	GNSS
L001268-01	Yellow	Yellow	-
L001268-02	Yellow	Yellow	White



RADIATION PATTERNS - 4G/5G CELLULAR

Key

4G/5G Cellular Port 1 Measured in Free Space


4G/5G Cellular Port 2 Measured in Free Space

4G/5G Cellular Port 1 Measured with Ground Plane


4G/5G Cellular Port 2 Measured with Ground Plane

Note - A label on the antenna base indicates the direction of 0° for ease of orientation and placement.


Radiation Patterns at 698 MHz




Radiation Patterns at 750 MHz




Radiation Pattern at 850 MHz




Radiation Pattern at 960 MHz




Radiation Pattern at 1690 MHz




Radiation Pattern at 1800 MHz




Radiation Pattern at 1900 MHz






Radiation Pattern at 2100 MHz






Radiation Pattern at 2200 MHz






Radiation Pattern at 2300 MHz




Radiation Pattern at 2500 MHz




Radiation Pattern at 2600 MHz




Radiation Pattern at 2690 MHz




Radiation Pattern at 3300 MHz




Radiation Pattern at 3500 MHz



Radiation Pattern at 3800 MHz



PACKING INFORMATION



TE TECHNICAL SUPPORT CENTER

USA:	+1 (800) 522-6752
Canada:	+1 (905) 475-6222
Mexico:	+52 (0) 55-1106-0800
Latin/S. America:	+54 (0) 11-4733-2200
Germany:	+49 (0) 6251-133-1999
UK:	+44 (0) 800-267666
France:	+33 (0) 1-3420-8686
Netherlands:	+31 (0) 73-6246-999
China:	+86 (0) 400-820-6015

te.com

TE, TE Connectivity, TE connectivity (logo), and EVERY CONNECTION COUNTS are trademarks owned or licensed by the TE Connectivity plc family of companies. Other product names, logos, and company names mentioned herein may be trademarks of their respective owners.

While TE has made every reasonable effort to ensure the accuracy of the information in this document, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, complete, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE EXPRESSLY DISCLAIMS ALL IMPLIED WARRANTIES REGARDING THE INFORMATION CONTAINED HEREIN, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTIES OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. In no event will TE be liable for any direct, indirect, incidental, special or consequential damages arising from or related to recipient's use of the information. It is the sole responsibility of recipient of this information to verify the results of this information using their engineering and product environment. Recipient assumes any and all risks associated with the use of the information. Antenna performance may vary. TE is a component manufacturer, and customer and/or end-user is responsible for all end-use compliance and regulatory requirements.

©2025 TE Connectivity. All Rights Reserved.

08/25 Original