


KEMET Part Number: PEH200ZV4220MU2
(A351ST222M500A)

PEH200, Aluminum Electrolytic, 2,200 uF, 20%, 500 VDC, -40/+85°C



General Information

Supplier:	KEMET
Series:	PEH200
Dielectric:	Aluminum Electrolytic
Description:	Screw Terminal, Aluminum Electrolytic
RoHS:	Yes
AEC-Q200:	No
Notes:	Dimensions D And L Include Slewing. MS (MxS) = M12x16
Shelf Life:	156 Weeks

Dimensions

D	76.6mm +/-1mm
L	146mm +/-1mm
T	3.8mm NOM
S	32mm +/-0.5mm
F	15mm +/-0.5mm
DT	15mm NOM
G	13mm NOM
LT	153mm +/-1mm
Z	13mm NOM

Specifications

Capacitance:	2,200 uF
Capacitance Tolerance:	20%
Voltage DC:	500 VDC
Temperature Range:	-40/+85°C
Rated Temperature:	85°C
Life:	19000 Hrs (Rated Voltage And Ripple Current At 85C)
Resistance:	58 mOhms (100Hz 20C), 38 mOhms (100kHz 20C)
Ripple Current:	11.1 Amps (100Hz 85C), 33.7 Amps (10kHz 50C), 25.1 Amps (10kHz 40C)
Leakage Current:	7300 uA (5min 20°C)
Inductance:	17 nH (ESL)

Packaging Specifications

Weight:	800 g
Slewing:	Yes
Packaging:	Bulk, Bag
Packaging Quantity:	9