

SACC-CI-M8FS-6P SMD T - Contact carrier



1412223

<https://www.phoenixcontact.com/gb/products/1412223>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Contact carrier, 6-position, Socket, straight, M8, coding: A, PCB mounting, SMD reflow, this item is undergoing a smooth changeover, lead-free alternative in accordance with RoHS II without exception 6c (Pb < 0.1%) possible on request in advance

Your advantages

- Reduced mounting costs thanks to two-piece device connector
- Packaging available for automated pick and place assembly
- All common pin assignments and codings available
- Easy device integration thanks to mechanical port screw connections with threaded attachment, press-in contour or direct integration in the front plate
- Optional shield connection and seal for the device when not plugged in

Commercial data

Item number	1412223
Packing unit	60 pc
Minimum order quantity	60 pc
Sales key	ABQHCS
Product key	ABQHCS
GTIN	4046356988322
Weight per piece (including packing)	2.88 g
Weight per piece (excluding packing)	2.122 g
Customs tariff number	85366990
Country of origin	DE

Technical data

Notes

Notes on operation	The electrical and mechanical data specified assume that the connector pair is correctly locked and mounted. If the connector is unlocked and if there is a danger of contamination, the connector must be sealed using a protective cap > IP54. Influences arising from litz wires, cables or PCB assembly must also be taken into consideration.
--------------------	--

Product properties

Product type	Contact insert
Application	Signal
Number of positions	6
Seal present	no
Shielded	no
Coding	A
Thread type	M8

Insulation characteristics

Overvoltage category	III
Degree of pollution	3

Electrical properties

Rated surge voltage	0.8 kV
Nominal voltage U_N	30 V AC 30 V DC
Nominal current I_N	1.5 A

Connection data

Connection method	SMD reflow
-------------------	------------

Material specifications

Flammability rating according to UL 94	V0
Contact material	CuZn
Contact surface material	Au
Contact carrier material	PA

Connector

Connection 1

Head design	Socket
Head cable outlet	straight
Head thread type	M8
Coding	A

SACC-CI-M8FS-6P SMD T - Contact carrier



1412223

<https://www.phoenixcontact.com/gb/products/1412223>

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	> 100
-----------------------------	-------

Environmental and real-life conditions

Ambient conditions

Degree of protection (when plugged in)	IP67 (correctly plugged in and locked)
Degree of protection	IP67 (correctly plugged in and locked)
	IP67, when plugged in
Ambient temperature (operation)	-55 °C ... 105 °C (Plug / socket)
	-55 °C ... 105 °C (without mechanical actuation)

Standards and regulations

Standard designation	M8 circular connector
Standards/specifications	according to IEC 61076-2-104

Mounting

Mounting type	PCB mounting
---------------	--------------

Packaging specifications

Type of packaging	Tray
-------------------	------

SACC-CI-M8FS-6P SMD T - Contact carrier


1412223

<https://www.phoenixcontact.com/gb/products/1412223>



Drawings

Schematic diagram



Pin assignment M8 socket, 6-pos.

SACC-CI-M8FS-6P SMD T - Contact carrier



1412223

<https://www.phoenixcontact.com/gb/products/1412223>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/1412223>

	cULus Recognized Approval ID: E221474-20160506			
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
	30 V	1.5 A	-	-

SACC-CI-M8FS-6P SMD T - Contact carrier



1412223

<https://www.phoenixcontact.com/gb/products/1412223>

Classifications

ECLASS

ECLASS-13.0	27440110
-------------	----------

ETIM

ETIM 9.0	EC003557
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

SACC-CI-M8FS-6P SMD T - Contact carrier



1412223

<https://www.phoenixcontact.com/gb/products/1412223>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk