



 PRODUCT-DETAILS

OT315E22WP

OT315E22WP SWITCH-DISCONNECTOR



General Information

Extended Product Type	OT315E22WP
Product ID	1SCA022810R0900
EAN	6417019272696
Catalog Description	OT315E22WP SWITCH-DISCONNECTOR
Long Description	4-pole, front operated, base mounted switch-diconductor with black IP65 handle and shaft, wide phase distance, terminal bolt kit included

ABB EcoSolutions

End Of Life Disassembling Instructions	1SCC301118M0201
Environmental Information	1SCC301266D0201
Environmental Product Declaration - EPD	1SCC301283D0201

Material Compliance

Conflict Minerals Reporting Template (CMRT)	9AKK108467A5658
REACH Declaration	1SCC011021D0201
RoHS Declaration	1SCC011020D0201
RoHS Information	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019
Toxic Substances Control Act - TSCA	1SCC011025D0201

Popular Downloads

Data Sheet, Technical Information	1SCC301020C0201
Instructions and Manuals	1SCC301035M0019
Environmental Product Declaration - EPD	1SCC301283D0201

Environmental

Degree of Protection	Front IP00
Environmental Information	1SCC301266D0201
Pollution Degree	3

Ordering

Minimum Order Quantity	1 piece
Customs Tariff Number	85365080
Country or Territory of Origin	Finland

Dimensions

Product Net Width	275 mm
Product Net Height	185 mm
Product Net Depth / Length	107 mm
Product Net Weight	4.3 kg 9.6 lb

Container Information

Package Level 1 Units	box 1 piece
Package Level 1 Width	250 mm 9.8 in
Package Level 1 Depth / Length	290 mm 11.4 in
Package Level 1 Height	170 mm 6.7 in
Package Level 1 Gross Weight	4.6 kg 10.2 lb
Package Level 1 EAN	6417019272696

Technical

Conventional Free-air Thermal Current (I_{th})	$\Theta = 40\text{ °C}$ 315 A
Conventional Thermal Current (I_{the})	Fully Enclosed 315 A
Degree of Protection	Front IP00
Distance Between Phases	Wide phase distance
Fourth Pole Position	Right Side
Fourth Pole Type	Switched - Simultaneous Function
Handle Color	Black
Handle Type	Handle and shaft included
Mechanical Durability	16000
Mounting Type	Base mounting
Number of Poles	4P
Operating Mode	Front
Pollution Degree	3
Position of Line Terminals	Top In - Bottom Out Bottom In - Top Out
Power Loss	at Rated Operating Conditions per Pole 6.5 W
Rated Conditional Short-Circuit Current (I_{nc})	(500 A fuse, 500 V) 100 kA (500 A fuse, 690 V) 80 kA
Rated Impulse Withstand Voltage (U_{imp})	12 kV
Rated Insulation Voltage (U_i)	acc. to IEC/EN 60664-1 1000 V
Rated Operational Current AC-21A (I_e)	(380 ... 415 V) 315 A (500 V) 315 A (690 V) 315 A
Rated Operational Current AC-22A (I_e)	(380 ... 415 V) 315 A (500 V) 315 A (690 V) 315 A
Rated Operational Current AC-23A (I_e)	(380 ... 415 V) 315 A (500 V) 315 A (690 V) 315 A
Rated Operational Power AC-23A (P_e)	(220 ... 240 V) 100 kW (400 ... 415 V) 180 kW (500 V) 220 kW (690 V) 315 kW
Rated Operational Voltage	Main Circuit 1000 V
Rated Short-Circuit Making Capacity (I_{cm})	(690 V) 65 kA
Rated Short-time Withstand Current Low Voltage (I_{cw})	for 1 s 15 kA
Special Functions	Wide phase distance
Standards	IEC 60947-3
Switches Operating Mechanism	Mechanism Between the Poles 22 (Between the Poles)
Terminal Type	Lug terminals
Terminal Width	25 mm
Tightening Torque	acc. IEC 60947-1 30 ... 44 N·m

Technical UL/CSA

Tightening Torque

acc. IEC 60947-1 30 ... 44 N·m

Certificates and Declarations

A2L Certificate – IEC	1SCC301337D0201
ATEX Certificate	No certification needed
BV Certificate	1SCC301103D0201
Declaration of Conformity - CE	1SCC301135D2704
DNV GL Certificate	1SCC301174D0204
GL Certificate	1SCC301139D0201
LR Certificate	1SCC301144D0201
UL Certificate	No certification needed
VDE Certificate	No certification needed

External Classifications and Standards

Object Classification Code	Q
ETIM 9	EC000216 - Switch disconnecter (low voltage)
ETIM 10	EC000216 - Switch disconnecter (AC)
UNSPSC	39122221
eClass	V11.1 : 27371403
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
E-Number (Finland)	3660827

Categories

Low Voltage Products and Systems → Switches → Switch Disconnectors

