



VARIABLE 3-SPEED FAN SETTING



OSCILLATING FUNCTION ON/OFF SWITCH



HANDLE FOR ADJUSTING TILTING HEAD



ADJUSTABLE HEIGHT FAN STAND



WEIGHTED PRESSED STEEL
BASE FOR STABILITY

ITEM. 05633

SIP 18" OSCILLATING PEDESTAL FAN

OSCILLATING PEDESTAL FAN FOR POWERFUL INDOOR AIR CIRCULATION

PRODUCT OVERVIEW

The **SIP 18" Oscillating Pedestal Fan** delivers powerful airflow to help cool spaces and circulate air in a variety of indoor environments.

This heavy-duty 3-blade fan is fitted with oscillating head to provide 180° of dynamic air coverage. A variable 3-speed fan setting and adjustable height column ensures suitable levels of air circulation can be maintained.

Fans are essential in helping to provide improved air quality to indoor spaces.

FEATURES & BENEFITS

✓ POWERFUL AIRFLOW

A heavy-duty 3-blade fan is powered from a 100w motor to deliver powerful and consistent airflow coverage.

✓ VARIABLE SPEED SETTINGS

3 settings for variable fan speed:

- **Low:** 900rpm
- **Medium:** 1100rpm
- **High:** 1300rpm

✓ OSCILLATING FAN HEAD

Adjustable fan head travels 180° on horizontal axis for dynamic circulation of air.

A weight pressed steel base ensures added stability when in operation.

THIS PRODUCT COMES WITH AN SIP 2-YEAR SILVER WARRANTY*

FIND OUT MORE AT SIP-GROUP.COM/WARRANTY



ITEM. 05633

SIP 18" OSCILLATING PEDESTAL FAN

FEATURES & BENEFITS CONT.

✓ ENHANCED FLEXIBILITY

Adjustable height pedestal (max. 145cm) ensures purposeful air circulation and coverage.
Extra-long power cable (2.5mtr) allows the fan to be easily moved and positioned for use.

✓ ENHANCED SAFETY FEATURES

Fan blades are fully enclosed with solid mesh steel guarding for greater user safety.

APPLICATIONS & USES

**DELIVERS POWERFUL & OSCILLATING VARIABLE
SPEED AIR CIRCULATION TO INDOOR SPACES**

**PERFECT FOR INDOOR AREAS SUCH AS OFFICES,
WORKSHOPS OR DOMESTIC USES**

ITEM NO.	05633		
INPUT SUPPLY	230v (13A)		
MOTOR POWER	100w (0.13hp)		
POWER CABLE	250cm		
FAN DIAMETER	Ø 18" (457mm)		
SPEED SETTINGS	3 speed settings		
	Low	Medium	High
	900rpm	1100rpm	1300rpm
NOISE LEVEL	66dB(A)		
NET WEIGHT	10.76kg		
GROSS WEIGHT	12.27kg		
PRODUCT DIMENSIONS	1550(H) x 510(W) x 505mm(D)		
PACKAGED DIMENSIONS	790(H) x 590(W) x 230mm(D)		