


## FEATURES

- **Material Composition:** Constructed from Fluorinated Ethylene Propylene, Fluoroelastomer, and Viton for superior chemical resistance
- **Temperature Range:** Operates effectively from -20 °C to 140 °C, ensuring versatility in various conditions
- **Hardness:** Shore A 90 to 95 provides optimal flexibility and strength
- **Size Specifications:** Inside diameter of 88.27 mm and outside diameter of 98.93 mm for precise fitting
- **Thickness:** 5.33 mm thickness enhances sealing capability

**RS PRO 88.27 mm O-Ring Seal, Shore A 90 to 95**

RS Stock No: 731-393



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

This RS PRO O-Ring Seal is designed for reliable sealing in a variety of industrial applications. Made from high-quality materials such as Fluorinated Ethylene Propylene, Fluoroelastomer, and Viton, it offers excellent resistance to chemicals and extreme temperatures. Ideal for use in environments where durability and performance are critical.

## General Specifications

|              |                  |
|--------------|------------------|
| Colour       | Black            |
| Hardness     | Shore A 90 to 95 |
| Product Type | O-Ring Seal      |
| Sub Type     | O-Ring           |

## Mechanical Specifications

|                  |  |
|------------------|--|
| Inside Diameter  | 88.27 mm   |
| Material         | Fluorinated Ethylene Propylene, Fluoroelastomer, Viton |
| Outside Diameter | 98.93 mm   |
| Thickness        | 5.33 mm  |

## Operation Environment Specifications

|                               |        |
|-------------------------------|--------|
| Maximum Operating Temperature | 140 °C |
| Minimum Operating Temperature | -20 °C |

## Approvals

|                     |   |
|---------------------|---|
| Standards/Approvals | BS ISO 3601-1, AS 568, EC 1935:2004, FDA, ISO 14001:2015, ISO 45001:2015, ISO 9001:2015, LABS, TSCA, USP Class VI, WRAS |
|---------------------|---|

