



ENGLISH

Datasheet

Stock No: 476-719

# RS Pro SPDT PCB Mount Non-Latching Relay Through Hole, 12V dc



## Product Details

### Low Profile Relays

Low profile: 15.7mm max height

8 and 16A versions have 5mm pinning, 12A has 3.5mm pinning

5kV dielectric strength (between coil and contacts)

Surge voltage up to 10kV (between coil and contacts)

Wash tight

Creepage distance 10mm

Conforms to VDE 0435/ 0631/ 0700

### Approvals

UL (File no. E134517), VDE (File no. 116934), CQC (File no. CQC02001001951)

### Standards

IEC 60335-1

## Specifications:

Coil Voltage	24V dc
Contact Configuration	SPDT
Mounting Type	PCB
Terminal Type	Through Hole
Coil Resistance	1440 $\Omega$
Application	Power
Length	29mm
Depth	12.7mm
Height	15.7mm
Dimensions	29 x 12.7 x 15.7mm
Contact Material	Silver Tin Oxide
Operating Temperature Range	-40 $\rightarrow$ +85°C
Minimum Operating Temperature	-40°C
Maximum Switching Power AC	4 kVA
Maximum Operating Temperature	+85°C