

**DMP21D0UFB4**

**20V P-CHANNEL ENHANCEMENT MODE MOSFET**

**Product Summary**

V <sub>(BR)DSS</sub>	R <sub>DS(on)</sub>	I <sub>D</sub> @ T <sub>A</sub> = 25°C
-20V	495mΩ @ V <sub>GS</sub> = -4.5V	-0.77A
	690mΩ @ V <sub>GS</sub> = -2.5V	-0.67A
	960mΩ @ V <sub>GS</sub> = -1.8V	-0.57A

**Description and Applications**

This MOSFET has been designed to minimize the on-state resistance (R<sub>DS(on)</sub>) and yet maintain superior switching performance, making it ideal for high efficiency power management applications.


- Portable electronics

**Features and Benefits**

- Footprint of just 0.6mm<sup>2</sup> – thirteen times smaller than SOT23
- 0.4mm profile – ideal for low profile applications
- Low Gate Threshold Voltage
- Fast Switching Speed
- **Totally Lead-Free & Fully RoHS compliant (Note 1)**
- **Halogen and Antimony Free. "Green" Device (Note 2)**
- **ESD Protected Gate 3KV**
- **Qualified to AEC-Q101 Standards for High Reliability**

**Mechanical Data**

- Case: X2-DFN1006-3
- Case Material: Molded Plastic, "Green" Molding Compound. UL Flammability Classification Rating 94V-0
- Moisture Sensitivity: Level 1 per J-STD-020
- Terminals: Finish – NiPdAu over Copper leadframe. Solderable per MIL-STD-202, Method 208
- Weight: 0.001 grams (approximate)




**Ordering Information (Note 3)**

Part Number	Marking	Reel size (inches)	Tape width (mm)	Quantity per reel
DMP21D0UFB4-7B	NO	7	8	10,000

- Notes:
1. No purposely added lead. Fully EU Directive 2002/95/EC (RoHS) & 2011/65/EU (RoHS 2) compliant.
  2. Halogen and Antimony free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.
  3. For packaging details, go to our website at <http://www.diodes.com>.

**Marking Information**

DMP21D0UFB4-7B



NO = Product Type Marking Code

Top View  
Bar Denotes Gate and Source Side

**Maximum Ratings** @T<sub>A</sub> = 25°C unless otherwise specified

Characteristic			Symbol	Value	Unit
Drain-Source Voltage			V <sub>DSS</sub>	-20	V
Gate-Source Voltage			V <sub>GSS</sub>	±8	V
Continuous Drain Current	Steady State	T <sub>A</sub> = 25°C (Note 4)	I <sub>D</sub>	-0.77	A
		T <sub>A</sub> = 85°C (Note 4)		-0.55	
		T <sub>A</sub> = 25°C (Note 5)		-1.17	
Pulsed Drain Current (Note 6)			I <sub>DM</sub>	-5.0	A

**Thermal Characteristics** @T<sub>A</sub> = 25°C unless otherwise specified

Characteristic			Symbol	Value	Unit
Power Dissipation (Note 4)			P <sub>D</sub>	0.43	W
Power Dissipation (Note 5)			P <sub>D</sub>	0.99	W
Thermal Resistance, Junction to Ambient (Note 4)			R <sub>θJA</sub>	293	°C/W
Thermal Resistance, Junction to Ambient (Note 5)			R <sub>θJA</sub>	126	°C/W
Operating and Storage Temperature Range			T <sub>J</sub> , T <sub>STG</sub>	-55 to +150	°C

**Thermal Characteristics**




Fig. 1 Single Pulse Maximum Power Dissipation




Fig. 2 Transient Thermal Response

**Electrical Characteristics** @T<sub>A</sub> = 25°C unless otherwise specified

Characteristic	Symbol	Min	Typ	Max	Unit	Test Condition
<b>OFF CHARACTERISTICS (Note 7)</b>						
Drain-Source Breakdown Voltage	BV <sub>DSS</sub>	20	-	-	V	V <sub>GS</sub> = 0V, I <sub>D</sub> = -250μA
Zero Gate Voltage Drain Current T <sub>J</sub> = 25°C	I <sub>DSS</sub>	-	-	-1	μA	V <sub>DS</sub> = -20V, V <sub>GS</sub> = 0V
Gate-Source Leakage	I <sub>GSS</sub>	-	-	±10	μA	V <sub>GS</sub> = ±8V, V <sub>DS</sub> = 0V
<b>ON CHARACTERISTICS (Note 7)</b>						
Gate Threshold Voltage	V <sub>GS(th)</sub>	-	-0.7	-	V	V <sub>DS</sub> = V <sub>GS</sub> , I <sub>D</sub> = -250μA
Static Drain-Source On-Resistance	R <sub>DS(ON)</sub>	-	-	495	mΩ	V <sub>GS</sub> = -4.5V, I <sub>D</sub> = -400mA
				690		V <sub>GS</sub> = -2.5V, I <sub>D</sub> = -300mA
				960		V <sub>GS</sub> = -1.8V, I <sub>D</sub> = -100mA
Forward Transfer Admittance	Y <sub>fs</sub>	50	-	-	mS	V <sub>DS</sub> = -3V, I <sub>D</sub> = -300mA
Diode Forward Voltage	V <sub>SD</sub>	-	-	-1.2	V	V <sub>GS</sub> = 0V, I <sub>S</sub> = -300mA
<b>DYNAMIC CHARACTERISTICS</b>						
Input Capacitance	C <sub>iss</sub>	-	76.5	-	pF	V <sub>DS</sub> = -10V, V <sub>GS</sub> = 0V, f = 1.0MHz
Output Capacitance	C <sub>oss</sub>	-	13.7	-	pF	
Reverse Transfer Capacitance	C <sub>rss</sub>	-	10.7	-	pF	
Gate Resistance	R <sub>g</sub>	-	195	-	Ω	V <sub>DS</sub> = 0V, V <sub>GS</sub> = 0V, f = 1MHz
Total Gate Charge	Q <sub>g</sub>	-	1.5	-	nC	V <sub>GS</sub> = -8V, V <sub>DS</sub> = -15V, I <sub>D</sub> = -1A
Total Gate Charge	Q <sub>g</sub>	-	1.0	-	nC	V <sub>GS</sub> = -4.5V, V <sub>DS</sub> = -15V, I <sub>D</sub> = -1A
Gate-Source Charge	Q <sub>gs</sub>	-	0.2	-	nC	
Gate-Drain Charge	Q <sub>gd</sub>	-	0.3	-	nC	
Turn-On Delay Time	t <sub>D(on)</sub>	-	7.1	-	ns	V <sub>DS</sub> = -10V, -I <sub>D</sub> = 1A V <sub>GS</sub> = -4.5V, R <sub>G</sub> = 6Ω
Turn-On Rise Time	t <sub>r</sub>	-	8.0	-	ns	
Turn-Off Delay Time	t <sub>D(off)</sub>	-	31.7	-	ns	
Turn-Off Fall Time	t <sub>f</sub>	-	18.5	-	ns	

- Notes:
- Device mounted on FR-4 substrate PC board, 2oz copper, with minimum recommended pad layout
  - Device mounted on FR-4 substrate PC board, 2oz copper, with thermal vias to bottom layer 1inch square copper plate
  - Device mounted on minimum recommended pad layout test board, 10μs pulse duty cycle = 1%.
  - Short duration pulse test used to minimize self-heating effect.

**Typical Characteristics**




Fig. 3 Typical Output Characteristic










Fig. 4 Typical Transfer Characteristic

**DMP21D0UFB4**



**DMP21D0UFB4**




Fig. 11 Typical Leakage Current vs. Drain-Source Voltage




Fig. 12 Leakage Current vs. Gate-Source Voltage




Fig. 13 Leakage Current vs. Gate-Source Voltage




Fig. 14 Typical Junction Capacitance




Fig. 15 Gate-Charge Characteristics



#### IMPORTANT NOTICE

DIODES INCORPORATED MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

Diodes Incorporated and its subsidiaries reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. Diodes Incorporated does not assume any liability arising out of the application or use of this document or any product described herein; neither does Diodes Incorporated convey any license under its patent or trademark rights, nor the rights of others. Any Customer or user of this document or products described herein in such applications shall assume all risks of such use and will agree to hold Diodes Incorporated and all the companies whose products are represented on Diodes Incorporated website, harmless against all damages.

Diodes Incorporated does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel. Should Customers purchase or use Diodes Incorporated products for any unintended or unauthorized application, Customers shall indemnify and hold Diodes Incorporated and its representatives harmless against all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized application.

Products described herein may be covered by one or more United States, international or foreign patents pending. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks.

#### LIFE SUPPORT

Diodes Incorporated products are specifically not authorized for use as critical components in life support devices or systems without the express written approval of the Chief Executive Officer of Diodes Incorporated. As used herein:

A. Life support devices or systems are devices or systems which:

1. are intended to implant into the body, or
2. support or sustain life and whose failure to perform when properly used in accordance with instructions for use provided in the labeling can be reasonably expected to result in significant injury to the user.

B. A critical component is any component in a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or to affect its safety or effectiveness.

Customers represent that they have all necessary expertise in the safety and regulatory ramifications of their life support devices or systems, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of Diodes Incorporated products in such safety-critical, life support devices or systems, notwithstanding any devices- or systems-related information or support that may be provided by Diodes Incorporated. Further, Customers must fully indemnify Diodes Incorporated and its representatives against any damages arising out of the use of Diodes Incorporated products in such safety-critical, life support devices or systems.

Copyright © 2012, Diodes Incorporated

[www.diodes.com](http://www.diodes.com)