

Power cable M8, PUR cable both ends assembled with M8 connector and M8 socket, 4-pole, Length 5.0m



Figure similar

General information	
Product description	Flexible cable (4-core), preassembled at each end with a 4-pin M8 male / female connector
Suitability for use	For connection to ET 200AL for 24 V DC power supply
Degree and class of protection	
IP degree of protection	IP65/67
Ambient conditions	
Ambient temperature during assembly, min.	-25 °C
Ambient temperature during assembly, max.	80 °C
Ambient temperature during storage/transportation	
• min.	-25 °C
• max.	80 °C
Cables	
Cable designation	LIF9Y11YFHF 4x 0.50 mm ²
Cable length	5 m
Number of electrical cores	4

Outer diameter of inner conductor	1 mm
Outer diameter of core insulation	1.46 mm
Outer diameter of cable sheath	5.1 mm
Number of bending cycles	2 000 000; Cable carrier compliant for 2 million bending cycles with a bending radius of 51 mm, a speed of 5 m/s and an acceleration of 5 m/s ²
Permissible bending radius, single bend, min.	26 mm
Permissible bending radius, multiple bends, min.	51 mm
Bending radius for continuous bending	51 mm
Color of cable sheath	gray
Color of core insulation of energy core	white / brown / blue / black
Weight per length	44 kg/km

Mechanics/material

Outgoing feeder type	180 degree cable outlet
Material of housing	plastic
Material of cable sheath	PE-PUR
Material of core insulation	PP
Material property	
• Halogen-free	Yes
• Silicone-free	Yes

last modified: 05/13/2020