




TE Internal #: 1939870-1

Secure Digital, 9 Position, 1.7 mm / 2.4 mm / 2.5 mm [.06 in / .09 in / .1 in] Centerline, Right Angle, -25 – 85 °C [-13 – 185 °F], SD Card Connectors

[View on TE.com >](#)

Connectors > PCB Connectors > Memory Card Connectors > SD Card Connectors



Compatible Card: **Secure Digital**

Number of Positions: **9**

Centerline (Pitch): **1.7 mm, 2.4 mm, 2.5 mm [.06 in, .09 in, .1 in]**

PCB Mount Orientation: **Right Angle**

Operating Temperature Range: **-25 – 85 °C [-13 – 185 °F]**

## Features

### Product Type Features

Connector & Contact Terminates To	Printed Circuit Board
Compatible Card	Secure Digital

### Configuration Features

Number of Rows	1
Number of Positions	9
PCB Mount Orientation	Right Angle

### Body Features

Primary Product Color	Black
-----------------------	-------

### Contact Features

Contact Current Rating (Max)	.5 A
Contact Underplating Material	Nickel
Contact Layout	Inline
Contact Mating Area Plating Material	Gold (Au)
Contact Base Material	Copper Alloy



PCB Contact Termination Area Plating Material	Tin
---	-----

Contact Mating Area Plating Material Thickness	.2 – .5 μm
--	------------

### Termination Features

Termination Method to PCB	Surface Mount
---------------------------	---------------

### Mechanical Attachment

Connector Mounting Type	Board Mount
-------------------------	-------------

### Housing Features

Housing Material	Liquid Crystal Polymer (LCP)
------------------	------------------------------

Shell Material	Copper Alloy
----------------	--------------

Centerline (Pitch)	1.7 mm, 2.4 mm, 2.5 mm [.06 in][.09 in][.1 in]
--------------------	--

### Dimensions

Profile Height from PCB	2.95 mm [.116 in]
-------------------------	-------------------

### Usage Conditions

Operating Temperature Range	-25 – 85 °C [-13 – 185 °F]
-----------------------------	----------------------------

### Operation/Application

Circuit Application	Signal
---------------------	--------

### Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

### Packaging Features

Packaging Method	Tape & Reel
------------------	-------------

## Product Compliance

For compliance documentation, visit the product page on [TE.com](https://www.te.com)>

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------

EU ELV Directive 2000/53/EC	Compliant
-----------------------------	-----------

China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
---	---

EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JAN 2023 (233) Does not contain REACH SVHC
--	--

Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC
-----------------	---

Free

Solder Process Capability

Reflow solder capable to 245°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

### Compatible Parts



TE Part # 1871916-1  
SD RVS 0H EMBOSS ASSY



TE Part # 1939115-1  
SD CONN STD EMBOSS W/B REVERSE

### Customers Also Bought




TE Part #5677954003  
RNF-3000-24/8-X-SP



TE Part #CAT-FSS0006  
3/4BSP M X F BRASS WATER FLOW SWITCH




TE Part #382229-019  
44A1121-20-0/9-9




TE Part #84952-6  
1MM FPC HORZ.BTTM CONT.ASS.6P



TE Part #1052422-1  
2052 0000 02,SMA FM JACK RECPT



TE Part #1057290-1  
3052 1201 10,N SERIES FM PLUG



TE Part #1376421-1  
10mm B-T-W Conn. 2P HDR ASSEMB



TE Part #2-2013289-1  
EMBOSS TAPE DDR3 204P 5.2H STD



## Documents

### Product Drawings

#### SD CARD CONNECTOR EMBOSS ASSY

Japanese

### CAD Files

#### Customer View Model

[ENG\\_CVM\\_CVM\\_1939870-1\\_B.2d\\_dxf.zip](#)

English

#### 3D PDF

3D

#### Customer View Model

[ENG\\_CVM\\_CVM\\_1939870-1\\_B.3d\\_igs.zip](#)

English

#### Customer View Model

[ENG\\_CVM\\_CVM\\_1939870-1\\_B.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

### Product Specifications

#### Product Specification

English

#### Product Specification

English