

# MCC 1/ 7-STZF-3,81 - PCB connector



1852419

<https://www.phoenixcontact.com/gb/products/1852419>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



PCB connector, nominal cross section: 1 mm<sup>2</sup>, color: green, nominal current: 8 A, rated voltage (III/2): 160 V, contact connection type: Socket, number of potentials: 7, number of rows: 1, number of positions: 7, number of connections: 7, product range: MCC 1/-STZF, pitch: 3.81 mm, connection method: Crimp connection, conductor/PCB connection direction: 0 °, plug-in system: COMBICON MC 1,5, locking: Screw locking mechanism, mounting method: Screw flange, type of packaging: packed in cardboard, Corresponding female crimp contacts with current [A] and conductor cross section range [mm<sup>2</sup>] data: 5A/MCC-MT 0,2-0,35 (1859988); 8A/MCC-MT 0,5-1,0 (1859991)

## Your advantages

- Inexpensive connection of large quantities of preassembled conductors
- Screwable flange for superior mechanical stability
- Pull-out aid facilitates handling and allows the tensile force to be reduced at the contact point

## Commercial data

|                                      |                                |
|--------------------------------------|--------------------------------|
| Item number                          | 1852419                        |
| Packing unit                         | 50 pc                          |
| Minimum order quantity               | 50 pc                          |
| Note                                 | Made to order (non-returnable) |
| Sales key                            | AABCAB                         |
| Product key                          | AABCAB                         |
| Catalog page                         | Page 207 (C-1-2013)            |
| GTIN                                 | 4017918132859                  |
| Weight per piece (including packing) | 2.999 g                        |
| Weight per piece (excluding packing) | 2.939 g                        |
| Customs tariff number                | 85366990                       |
| Country of origin                    | PL                             |

# MCC 1/ 7-STZF-3,81 - PCB connector



1852419

<https://www.phoenixcontact.com/gb/products/1852419>

## Technical data

### Product properties

|                       |                       |
|-----------------------|-----------------------|
| Product type          | PCB connector         |
| Product family        | MCC 1/...-STZF        |
| Product line          | COMBICON Connectors S |
| Type                  | Standard              |
| Number of positions   | 7                     |
| Pitch                 | 3.81 mm               |
| Number of connections | 7                     |
| Number of rows        | 1                     |
| Number of potentials  | 7                     |
| Mounting flange       | Screw flange          |

### Electrical properties

#### Properties

|                             |        |
|-----------------------------|--------|
| Nominal current $I_N$       | 8 A    |
| Nominal voltage $U_N$       | 160 V  |
| Rated voltage (III/3)       | 160 V  |
| Rated surge voltage (III/3) | 2.5 kV |
| Rated voltage (III/2)       | 160 V  |
| Rated surge voltage (III/2) | 2.5 kV |
| Rated voltage (II/2)        | 320 V  |
| Rated surge voltage (II/2)  | 2.5 kV |

### Connection data

#### Connection technology

|                         |                   |
|-------------------------|-------------------|
| Type                    | Standard          |
| Connector system        | COMBICON MC 1,5   |
| Nominal cross section   | 1 mm <sup>2</sup> |
| Contact connection type | Socket            |

#### Interlock

|                 |                         |
|-----------------|-------------------------|
| Locking type    | Screw locking mechanism |
| Mounting flange | Screw flange            |

#### Conductor connection

|                                    |                                           |
|------------------------------------|-------------------------------------------|
| Connection method                  | Crimp connection                          |
| Conductor/PCB connection direction | 0 °                                       |
| Conductor cross section flexible   | 0.2 mm <sup>2</sup> ... 1 mm <sup>2</sup> |
| Conductor cross section AWG        | 24 ... 18                                 |

### Material specifications

# MCC 1/ 7-STZF-3,81 - PCB connector



1852419

<https://www.phoenixcontact.com/gb/products/1852419>


## Material data - contact

|                                        |          |
|----------------------------------------|----------|
| Metal surface contact area (top layer) | Tin (Sn) |
|----------------------------------------|----------|

## Material data - housing

|                                                                   |              |
|-------------------------------------------------------------------|--------------|
| Color (Housing)                                                   | green (6021) |
| Insulating material                                               | PA           |
| Insulating material group                                         | I            |
| CTI according to IEC 60112                                        | 600          |
| Flammability rating according to UL 94                            | V0           |
| Glow wire flammability index GWFI according to EN 60695-2-12      | 850          |
| Glow wire ignition temperature GWIT according to EN 60695-2-13    | 775          |
| Temperature for the ball pressure test according to EN 60695-10-2 | 125 °C       |

## Dimensions

|                     |                                                                                      |
|---------------------|--------------------------------------------------------------------------------------|
| Dimensional drawing |  |
| Pitch               | 3.81 mm                                                                              |
| Width [w]           | 37.06 mm                                                                             |
| Height [h]          | 8.7 mm                                                                               |
| Length [l]          | 23.1 mm                                                                              |

## Environmental and real-life conditions

### Ambient conditions

|                                         |                                                     |
|-----------------------------------------|-----------------------------------------------------|
| Ambient temperature (operation)         | -40 °C ... 100 °C (dependent on the derating curve) |
| Ambient temperature (storage/transport) | -40 °C ... 70 °C                                    |
| Relative humidity (storage/transport)   | 30 % ... 70 %                                       |
| Ambient temperature (assembly)          | -5 °C ... 100 °C                                    |

## Electrical tests

### Air clearances and creepage distances |

|                                                        |                     |
|--------------------------------------------------------|---------------------|
| Specification                                          | IEC 60664-1:2007-04 |
| Insulating material group                              | I                   |
| Comparative tracking index (IEC 60112)                 | CTI 600             |
| Rated insulation voltage (III/3)                       | 160 V               |
| Rated surge voltage (III/3)                            | 2.5 kV              |
| minimum clearance value - non-homogenous field (III/3) | 1.5 mm              |
| minimum creepage distance (III/3)                      | 2 mm                |
| Rated insulation voltage (III/2)                       | 160 V               |

# MCC 1/ 7-STZF-3,81 - PCB connector



1852419

<https://www.phoenixcontact.com/gb/products/1852419>


|                                                        |        |
|--------------------------------------------------------|--------|
| Rated surge voltage (III/2)                            | 2.5 kV |
| minimum clearance value - non-homogenous field (III/2) | 1.5 mm |
| minimum creepage distance (III/2)                      | 1.5 mm |
| Rated insulation voltage (II/2)                        | 320 V  |
| Rated surge voltage (II/2)                             | 2.5 kV |
| minimum clearance value - non-homogenous field (II/2)  | 1.5 mm |
| minimum creepage distance (II/2)                       | 1.6 mm |

## Packaging specifications


|                   |                     |
|-------------------|---------------------|
| Type of packaging | packed in cardboard |
|-------------------|---------------------|

## Drawings

Dimensional drawing



Diagram



Type: MCC 1/...-ST-3,81 with MC 1,5/...-G-3,81; contact: MCC-MT 0,5 - 1,0

# MCC 1/ 7-STZF-3,81 - PCB connector



1852419

<https://www.phoenixcontact.com/gb/products/1852419>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/1852419>

|  <b>cULus Recognized</b><br>Approval ID: E60425-20110128 |                       |                       |                   |                             |
|-------------------------------------------------------------------------------------------------------------------------------------------|-----------------------|-----------------------|-------------------|-----------------------------|
|                                                                                                                                           | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
| Use group B                                                                                                                               | 300 V                 | 5 A                   | 24 - 22           | -                           |
|                                                                                                                                           |                       |                       |                   |                             |
| Use group D                                                                                                                               | 300 V                 | 5 A                   | 24 - 22           | -                           |
|                                                                                                                                           |                       |                       |                   |                             |

# MCC 1/ 7-STZF-3,81 - PCB connector



1852419

<https://www.phoenixcontact.com/gb/products/1852419>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27460202 |
|-------------|----------|

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC002638 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# MCC 1/ 7-STZF-3,81 - PCB connector



1852419

<https://www.phoenixcontact.com/gb/products/1852419>

## Environmental product compliance

### EU RoHS

|                                         |                    |
|-----------------------------------------|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|-----------------------------------------|--------------------|

### China RoHS

|                                        |                                          |
|----------------------------------------|------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|                                        | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

### EF3.0 Climate Change

|         |               |
|---------|---------------|
| CO2e kg | 0.037 kg CO2e |
|---------|---------------|

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd  
Halesfield 13, Telford  
Shropshire, TF7 4PG  
01952 681700  
[info@phoenixcontact.co.uk](mailto:info@phoenixcontact.co.uk)