

WML-FLAG 6 (30X10)R - Cable marking flags



0830712

<https://www.phoenixcontact.com/gb/products/0830712>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable marking flags, Roll, white, unlabeled, can be labeled with: THERMOMARK E.300 (D)/600 (D), THERMOMARK ROLL 2.0, THERMOMARK ROLL, THERMOMARK ROLL X1, THERMOMARK ROLLMaster 300/600, THERMOMARK X1.2, mounting type: adhesive, cable diameter: ≤ 6 mm, Number of individual labels: 2500, text field height: 10 mm, text field width: 30 mm

Your advantages

- Self-adhesive conductor marking as a flag
- High-quality marking created by the thermal transfer printer
- Resistant to solvents
- Can be printed on both sides

Commercial data

Item number	0830712
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BG2211
Product key	BG2211
Catalog page	Page 219 (C-3-2019)
GTIN	4046356724562
Weight per piece (including packing)	672 g
Weight per piece (excluding packing)	666.5 g
Customs tariff number	39199080
Country of origin	US

WML-FLAG 6 (30X10)R - Cable marking flags



0830712

<https://www.phoenixcontact.com/gb/products/0830712>

Technical data

Product properties

Product type	Conductor marking
Type	Label

Marking

Number of individual labels	2500
Number of individual labels per row	1
Identification technology	Thermal transfer for rolls

Dimensions

Width	10 mm
Length	30 mm

External dimensions

Outside diameter	0.5 mm ... 6 mm
------------------	-----------------

Text field

Text field width	30 mm
Text field height	10 mm

Material specifications

Color	white (RAL 9010)
Material	Polyolefine
Base element material	Vinyl film
Components	free from silicone and halogen

Cable/line

External cable diameter	≤ 6.00 mm
	6 mm

Environmental and real-life conditions

UV resistance

Specification	ISO 4892-2:2013-03 (following)
Result	Test passed
Test duration	96 h

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-1):2011-07
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Isopropyl [CAS No. 67-63-0]	Test passed

Ambient conditions

Ambient temperature (operation)	-40 °C ... 60 °C
---------------------------------	------------------

WML-FLAG 6 (30X10)R - Cable marking flags



0830712

<https://www.phoenixcontact.com/gb/products/0830712>

Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 %

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Mounting

Mounting type	adhesive
---------------	----------

WML-FLAG 6 (30X10)R - Cable marking flags



0830712

<https://www.phoenixcontact.com/gb/products/0830712>

Classifications

ECLASS

ECLASS-13.0	27281102
-------------	----------

ETIM

ETIM 9.0	EC001530
----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

WML-FLAG 6 (30X10)R - Cable marking flags



0830712

<https://www.phoenixcontact.com/gb/products/0830712>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	4-(1,1,3,3-tetramethylbutyl)phenol, ethoxylated(CAS: n/a)
SCIP	f55eadac-8f62-4a4e-966c-f5d74248d8f1

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk