

ME 22,5 TBUS 1,5/ 5 VPE1 KMGY - DIN rail bus connectors



2202543

<https://www.phoenixcontact.com/in/products/2202543>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



DIN rail connector, color: light gray, nominal current: 8 A (parallel contacts), rated voltage (III/2): 125 V, number of positions: 5, product range: TBUS5-22,5..., pitch: 3.81 mm, mounting: DIN rail mounting, locking: without, mounting method: without, type of packaging: packed in cardboard, Item with gold-plated contacts, bus connectors for connecting with electronics housings, 5 parallel contacts

Your advantages

- Space-saving installation under the housing in the DIN rail
- Contact design enables electronics modules to be easily snapped on
- Power supply and communication without additional wiring
- Parallel and serial contacts for efficient signal and data transmission

Commercial data

Item number	2202543
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	ACH
Product key	ACHACA
GTIN	4055626142371
Weight per piece (including packing)	7 g
Weight per piece (excluding packing)	4.64 g
Customs tariff number	85366990
Country of origin	DE

ME 22,5 TBUS 1,5/ 5 VPE1 KMGY - DIN rail bus connectors



2202543

<https://www.phoenixcontact.com/in/products/2202543>

Technical data

Notes

Recommendation	Material of contact pads for bus connector, galvanic gold (hard gold)
----------------	---

Product properties

Product type	DIN rail connector
Product family	TBUS5-22,5..
Number of positions	5
Pitch	3.81 mm

Electrical properties

Properties

Nominal current I_N	8 A (parallel contacts)
Nominal voltage U_N	125 V
Contact resistance	4.4 mΩ
Rated surge voltage (III/3)	2.5 kV
Rated voltage (III/2)	125 V
Rated surge voltage (III/2)	2.5 kV
Rated voltage (II/2)	320 V
Rated surge voltage (II/2)	2.5 kV

Material specifications

Material data - contact

Contact material	Cu alloy
Surface characteristics	gold-plated

Material data - housing

Color (Housing)	light gray (7035)
Insulating material	PA
Insulating material group	I
CTI according to IEC 60112	600
Flammability rating according to UL 94	V0

material specifications - connector

Color ()	()
----------	----

Dimensions

Pitch	3.81 mm
Width [w]	29.2 mm
Height [h]	36.5 mm
Length [l]	20.45 mm

ME 22,5 TBUS 1,5/ 5 VPE1 KMGY - DIN rail bus connectors



2202543

<https://www.phoenixcontact.com/in/products/2202543>

Mounting

Mounting type	DIN rail mounting
---------------	-------------------

Mechanical tests

Insertion and withdrawal forces

Result	Test passed
No. of cycles	25
Insertion strength per pos. approx.	6 N
Withdraw strength per pos. approx.	5 N

Contact holder in insert

Specification	IEC 60512-15-1:2008-05
Contact holder in insert Requirements >20 N	Test passed

Polarization and coding

Specification	IEC 60512-13-5:2006-02
Result	Test passed

Visual inspection

Specification	IEC 60512-1-1:2002-02
Result	Test passed

Dimension check

Specification	IEC 60512-1-2:2002-02
Result	Test passed

Environmental and real-life conditions

Vibration test

Specification	IEC 60068-2-6:2007-12
Frequency	10 - 150 - 10 Hz
Sweep speed	1 octave/min
Amplitude	0.35 mm (10 Hz ... 60.1 Hz)
Acceleration	5g (60.1 Hz ... 500 Hz)
Test duration per axis	2.5 h
Test directions	X-, Y- and Z-axis (pos. and neg.)

Durability test

Specification	IEC 60512-9-1:2010-03
Impulse withstand voltage at sea level	2.95 kV
Contact resistance R ₁	4.4 mΩ
Contact resistance R ₂	4.5 mΩ
Insertion/withdrawal cycles	25

Climatic test

ME 22,5 TBUS 1,5/ 5 VPE1 KMGY - DIN rail bus connectors



2202543

<https://www.phoenixcontact.com/in/products/2202543>

Specification	ISO 6988:1985-02
Corrosive stress	0.2 dm ³ SO ₂ on 300 dm ³ /40 °C/1 cycle
Thermal stress	100 °C/168 h
Power-frequency withstand voltage	1.39 kV

Glow-wire test

Specification	IEC 60695-2-10:2013-04
Temperature	850 °C
Time of exposure	30 s

Shocks

Specification	IEC 60068-2-27:2008-02
Pulse shape	Semi-sinusoidal
Acceleration	15g
Shock duration	11 ms
Test directions	X-, Y- and Z-axis (pos. and neg.)

Ambient conditions

Ambient temperature (operation)	-40 °C ... 105 °C (dependent on the derating curve)
Ambient temperature (storage/transport)	-40 °C ... 55 °C
Relative humidity (storage/transport)	30 % ... 70 %
Ambient temperature (assembly)	-5 °C ... 100 °C

Electrical tests

Thermal test | Test group C

Specification	IEC 60512-5-1:2002-02
Tested number of positions	5

Air clearances and creepage distances |

Specification	IEC 60664-1:2007-04
Insulating material group	I
Rated surge voltage (III/3)	2.5 kV
minimum clearance value - non-homogenous field (III/3)	1.5 mm
minimum creepage distance (III/3)	1.9 mm
Rated insulation voltage (III/2)	125 V
Rated surge voltage (III/2)	2.5 kV
minimum clearance value - non-homogenous field (III/2)	1.5 mm
minimum creepage distance (III/2)	0.75 mm
Rated insulation voltage (II/2)	320 V
Rated surge voltage (II/2)	2.5 kV
minimum clearance value - non-homogenous field (II/2)	1.5 mm
minimum creepage distance (II/2)	1.6 mm

Packaging specifications

Type of packaging	packed in cardboard
-------------------	---------------------

ME 22,5 TBUS 1,5/ 5 VPE1 KMGY - DIN rail bus connectors



2202543

<https://www.phoenixcontact.com/in/products/2202543>

Outer packaging type	Carton
----------------------	--------

ME 22,5 TBUS 1,5/ 5 VPE1 KMGY - DIN rail bus connectors




2202543

<https://www.phoenixcontact.com/in/products/2202543>

Drawings

Diagram



Type: TBUS5...

ME 22,5 TBUS 1,5/ 5 VPE1 KMGY - DIN rail bus connectors



2202543

<https://www.phoenixcontact.com/in/products/2202543>

Classifications

ECLASS

ECLASS-11.0	27460201
ECLASS-12.0	27460201
ECLASS-13.0	27460201

ETIM

ETIM 9.0	EC002637
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

ME 22,5 TBUS 1,5/ 5 VPE1 KMGY - DIN rail bus connectors



2202543
<https://www.phoenixcontact.com/in/products/2202543>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

ME 22,5 TBUS 1,5/ 5 VPE1 KMGY - DIN rail bus connectors



2202543

<https://www.phoenixcontact.com/in/products/2202543>

Accessories

E/ME TBUS NS35 GY - End bracket

2713780

<https://www.phoenixcontact.com/in/products/2713780>



End clamp, stable construction for DIN rail bus connector

ME MAX 22,5 2-2 DEV-KIT KMGY - Housing set

2202524

<https://www.phoenixcontact.com/in/products/2202524>



DEV-KIT ME MAX: contains 1 x ME MAX 22,5 2-2 housing and pluggable connection technology (4x MSTBO with 4x MSTBT), supplied in individual parts

ME 22,5 TBUS 1,5/ 5 VPE1 KMGY - DIN rail bus connectors



2202543


<https://www.phoenixcontact.com/in/products/2202543>

ME MAX/16 2-2 TBUS DEV-PCB - PCB

2202542

<https://www.phoenixcontact.com/in/products/2202542>

Perfboard for the ME-MAX DEV-KIT; for 4-pos. MSTBO header; ideal for manual soldering



Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.

A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420

info@phoenixcontact.co.in