

Han 10B-HMC-asg2-LB-M32



Image is for illustration purposes only. Please refer to product description.

Part number	19 30 210 0292
Specification	Han 10B-HMC-asg2-LB-M32
HARTING eCatalogue	https://harting.com/19302100292

Identification

Category	Hoods / Housings
Series of hoods/housings	Han [®] HMC
Type of hood/housing	Surface mounted housing
Type	High construction

Version

Size	10 B
Version	Side entry
Number of cable entries	2
Cable entry	2x M32
Locking type	Single locking lever
Han-Easy Lock [®]	Yes
Field of application	Special hoods and housings for high mating cycles

Technical characteristics

Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Mating cycles	≥10,000
Note on the mating cycles	Mating cycles with other HMC components
Degree of protection acc. to IEC 60529	IP65



Pushing Performance
Since 1945

Technical characteristics

	4
Type rating acc. to UL 50 / UL 50E	4X
	12

Material properties

Material (hood/housing)	Aluminium die-cast
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 7037 (dust grey)
Material (seal)	NBR
Material (locking)	Polycarbonate (PC) Stainless steel
Colour (locking)	RAL 7037 (dust grey)
Material flammability class acc. to UL 94 (locking levers)	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Potassium 1,1,2,2,3,3,4,4,4-nonafluorobutane-1-sulphonate
ECHA SCIP number	60b1a572-bb3f-476f-9307-b7d1688bd90c
California Proposition 65 substances	Yes
California Proposition 65 substances	Nickel Naphthalene
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R22 (HL 1-3) R23 (HL 1-3)

Specifications and approvals

Approvals	DNV GL
-----------	--------

Commercial data

Packaging size	1
Net weight	338.75 g
Country of origin	Germany



Pushing Performance
Since 1945

Commercial data

European customs tariff number	85389099
GTIN	5713140127548
eCl@ss	27440202 Shell for industrial connectors
ETIM	EC000437
UNSPSC 24.0	39121466