


TE Internal #: 1-282841-2
12 Position PCB Terminal Block, Header, Wire-to-Board, 5.08 mm [.2 in] Centerline, 1 Row, 90° Wire Entry Angle, 30 – 12 AWG, .05 – 3 mm² Wire, 300 VAC

[View on TE.com >](#)



Connectors > Terminal Blocks & Strips > PCB Terminal Blocks



Number of Positions: 12
Terminal Block Connector Type: Header
Connector System: Wire-to-Board
Centerline (Pitch): 5.08 mm [.2 in]
Number of Rows: 1

Features

Product Type Features

Wire Protection	With
Terminal Block Connector Type	Header
Connector System	Wire-to-Board
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Stacked Levels	Without
Number of Positions	12
Number of Rows	1
Wire Entry Angle	90°
Wire Entry Location	Side

Electrical Characteristics

Operating Voltage	300 VAC
-------------------	---------

Body Features

Primary Product Color	Green
-----------------------	-------



Product Orientation	Vertical
---------------------	----------

Contact Features

Contact Mating Area Plating Material	Tin (Sn)
Contact Base Material	Brass
Contact Current Rating (Max)	17.5 A

Termination Features

Termination Post & Tail Length	3.5 mm[.138 in]
Termination Method to PCB	Through Hole - Solder

Mechanical Attachment

Screw Plating Material	Nickel
Screw Material	Brass
Thread Size	M3
Connector Mounting Type	Board Mount

Housing Features

Housing Material	PA 66
Centerline (Pitch)	5.08 mm[.2 in]

Dimensions

Wire Size	30 – 12 AWG
-----------	-------------

Usage Conditions

Operating Temperature Range	-40 – 110 °C[-40 – 230 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Packaging Features

Packaging Method	Box
Packaging Quantity	100

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold



EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JAN 2025 (247)
Candidate List Declared Against: JAN 2025 (247)
SVHC > Threshold:
Pb (3% in Component Part)
Article Safe Usage Statements:
Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content

Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free


Solder Process Capability

Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1-796949-2

12POS TERMI-BLOK PCB MOUNT

Customers Also Bought




TE Part #5-534237-2

04 MODII VRT SR CE 100/115



TE Part #2301994-1

RJ45 JACK INT.MAG. 10/100 1X1 INV.



TE Part #1623802-4

SQZ15 5K 5% (METAL FILM)



TE Part #5-104655-9

80 50/50 HDR DRST SFMNT TIN




TE Part #1-1734248-0
1.0 FPC, ZIF V/T, SMT, 10P




TE Part #2301845-2
AMPL REC HD20, R/A, 15P, B/L, 4-40 A /LOCK



TE Part #1-2176326-3
CRGP 0603 100R 1%



TE Part #5-104652-8
80 50/50 GRID DRST SFMNT RCPT



TE Part #5-103634-3
04 MTE HDR SRRA LATCH.100CL LF



TE Part #1612773-4
SEMI-HARD TRAY DDR2 SODIMM SOCKET 200P 6

Documents

Product Drawings

TERMI-BLOK PCB MOUNT 12P.5

English

CAD Files

Customer View Model

ENG_CVM_1-282841-2_H4.3d_igs.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_1-282841-2_H4.3d_stp.zip

English

Customer View Model

ENG_CVM_1-282841-2_H4.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-282841-2_C.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1-282841-2_C.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-282841-2_C.3d_stp.zip

English



By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

BUCHANAN TERMINAL BLOCKS CATALOG - EUROSTYLE TERMINAL BLOCKS

English

1-1773458-1_EURO_STYLE_TERMINAL_BLOCKS_QRG

English

Product Specifications

Application Specification

English

Agency Approvals

UL

English