

Endress+Hauser TMT72-AAA1AABA1

Terminal head or DIN rail mounted temperature transmitter with universal input for RTD and TC temperature assemblies. Programmable via HART® or Bluetooth®. Certified for hazardous areas.



Picture for reference only. Product appearance may vary based on configuration

The iTEMP TMT72 temperature transmitter transfers converted signals from RTD and thermocouple (TC) temperature probes, as well as resistance and voltage signals using HART communication. Diagnostics information according to NAMUR NE 107. Seamless integration into all major control and asset management systems. Integrated Bluetooth® interface for remote operation via Endress+Hauser SmartBlue App.

Configuration of TMT72-AAA1AABA1:

Approval:	AA	Non-hazardous area
Communication; Output Signal; Operation:	A	HART; 4-20mA; HART configuration
Housing Shape:	1	Form B head transmitter, DIN EN 50446
Electrical Connection:	A	Screw terminals
Field Housing:	AB	W/o, mounting set DIN terminal head
Device Model:	A1	1

Alternative part number: TMT72-13P0/0