Product datasheet

Specifications



FRONT PLATE ISFT100N VERTICAL WIDTH 600/650 8M

LVS03325

EAN Code: 3606481932938

Main

Range	PrismaSeT
Range of product	PrismaSeT G PrismaSeT P
Product or component type	Front plate
Accessory / separate part category	Installation accessory
Range compatibility	PrismaSeT PrismaSeT G enclosure PrismaSeT PrismaSeT P cubicle
Type of front plate	Cut-out
Installed device	FuPact: fixed ISFT100N - control: fuse carriers handle - vertical installation
Poles description	6 x 3P: busbars support: ISFT100N vertical installation 8 x 3P: mounting plate support: ISFT100N vertical installation
Operating position	Horizontal

Complementary

Enclosure/cubicle description	Floor-standing enclosure - width 600 mm Wall-mounted enclosure - width 600 mm Cubicle - width 650 mm
Connection position	Rear connection Direct connection
Number of vertical modules [50 mm]	8
Standards	IEC 61439-2 IEC 61439-1
Product certifications	ASTA
Material	Steel
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Surface finish	Matt Textured
Colour	White (RAL 9003)
Width	500 mm
Height	400 mm
Net weight	1.64 kg

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

functional unit	600 mm PrismaSeT G floor-standing enclosure FuPact ISFT100N fixed fuse carriers handle vertical 3P 6 rear connection on busbar 8 600 mm Prisma G wall-mounted enclosure FuPact ISFT100N fixed fuse carriers handle vertical 3P 6 rear connection on busbar 8 600 mm Prisma G floor-standing enclosure FuPact ISFT100N fixed fuse carriers handle vertical 3P 8 direct 8 600 mm Prisma G wall-mounted enclosure FuPact ISFT100N fixed fuse carriers handle vertical 3P 8 direct 8 650 mm 400 mm Prisma P cubicle FuPact ISFT100N fixed fuse carriers handle vertical 3P 8 direct 8 650 mm 400 mm Prisma P cubicle FuPact ISFT100N fixed fuse carriers handle vertical 3P 6 rear connection on busbar 8

Environment

IP degree of protection	IP30

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.000 cm
Package 1 Width	41.000 cm
Package 1 Length	51.500 cm
Package 1 Weight	1.612 kg
Unit Type of Package 2	CAR
Number of Units in Package 2	6
Package 2 Height	11.000 cm
Package 2 Width	42.500 cm
Package 2 Length	53.000 cm
Package 2 Weight	10.120 kg
Unit Type of Package 3	P12
Number of Units in Package 3	48
Package 3 Height	57.000 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	91.376 kg

Contractual warranty

Warranty (in months)	18

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

Environmental footprint

Environmental Disclosure	Product Environmental Profile

Use Better

Materials and Substances

Packaging made with recycled cardboard	Yes
Packaging without single use plastic	Yes
EU RoHS Directive	Compliant
REACh Regulation	Free of Substances of Very High Concern above the threshold
Halogen-free status	Halogen free plastic parts product
PVC free	Yes
Silicone-free	Yes

Use Longer

Lifetime extension

Repair	No

Use Again

Repack and remanufacture

End of life manual availability	No need of specific recycling operations
Take-back	No