



Connectors > PCB Connectors > Card Edge Connectors > Card Edge Power Connectors



Connector System: **Board-to-Board**

Number of Positions: **34**

Centerline (Pitch): **8.24 mm [.324 in]**

Contact Current Rating (Max): **62.5 A**

Circuit Application: **Power & Signal**

Features

Product Type Features

Connector & Contact Terminates To	Printed Circuit Board
Connector & Housing Type	Receptacle
Connector System	Board-to-Board

Configuration Features

Number of Positions	34
Number of Power Positions	10
Number of Signal Positions	24
Number of Dual Positions	5

Electrical Characteristics

Operating Voltage	250 V
-------------------	-------

Contact Features

Contact Type	Socket
Contact Mating Area Plating Material Thickness	.76 µm[30 µin]
Contact Current Rating (Max)	62.5 A
Contact Mating Area Plating Material	Gold (Au)



Termination Features

Termination Method to PCB	Through Hole - Solder
---------------------------	-----------------------

Mechanical Attachment

Connector Mounting Type	Board Mount
-------------------------	-------------

Housing Features

Centerline (Pitch)	8.24 mm[.324 in]
--------------------	------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought



TE Part #2-1879224-0
CPF 0603 4K75 0.1% 25PPM 1K RL

TE Part #1622866-1
CRG0603 1% 1K0

TE Part #2-2176246-0
CRGS2512 5% 39R

TE Part #8-1879223-5
CPF 0603 2K1 0.1% 25PPM 1K RL

TE Part #130130
SOLIS R 16-14 M6

TE Part #5645235-1
CONN SEC II 31 POS 100C/L

TE Part #1879252-8
RP 2B 4R99 0.1% 15PPM 1K RL

TE Part #5-1879134-0
RN 0603 32K4 0.1% 10PPM 1K RL

TE Part #4-2176057-6
RLP73K 3A R75 1% 1K RL

TE Part #5-1879224-5
CPF 0603 11K8 0.1% 25PPM 1K RL

Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2322260-1_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2322260-1_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2322260-1_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English

Agency Approvals



UL Report

English