

SHOWA

CN750

CHEMICAL PROTECTION

100% biodegradable nitrile gauntlet with high grip properties, length 32cm, 0.46mm thick


Offering high resistance to chemicals and excellent grip properties. 100% biodegradable using Eco Best Technology®

Features

- ▲ A fine, supple glove (0.46 mm thick)
- ▲ Nitrile protects the hand from oils, hydrocarbons and grease penetration
- ▲ Wave pattern finish provides a tactile feel, long-lasting grip and control in wet and oily conditions
- ▲ Flock-lined for extra comfort and ease of donning
- ▲ Eco Best Technology enables the glove to biodegrade once disposed of in landfill
- ▲ Innovative technology on the inside
- ▲ Impermeable for working in damp environments
- ▲ Designed for easy movement and continuous wear



Certifications



Suitable industries & applications

Industries

- ▲ Chemicals
- ▲ Construction
- ▲ Food Production
- ▲ Manufacturing
- ▲ Maritime

Applications

- ▲ Bottling and Canning
- ▲ Chemical Handling and Containment
- ▲ Commercial Fishing
- ▲ Commercial Washdown
- ▲ Component and Product Assembly
- ▲ Dairy
- ▲ Handling Wet
- ▲ Oily or Greasy Materials

Europe

sales@globus.com
+44 (0)161 877 4747
+44 (0)161 877 4746

Middle East & Africa

sales.gcc@globusgroup.com
+971 4 882 9962
+971 4 882 9963

Americas

salesusa@globusgroup.com
+1 83 337 54747

The descriptions, characteristics, applications and photos are given for information purposes and do not constitute a contractual commitment. The manufacturer reserves the right to make any modifications it deems necessary.

GLOBUS



CN750

CHEMICAL PROTECTION

100% biodegradable nitrile gauntlet with high grip properties, length 32cm, 0.46mm thick

Product information

Materials	Liner:	Cotton Flock
	Coating:	Nitrile
Colour	Blue	
Length	300mm	
Cuff Style	Gauntlet	

Ordering information

S	SHOCN7501	Items per Case 72 x Pairs
M	SHOCN7502	
L	SHOCN7503	
XL	SHOCN7504	
XXL	SHOCN7505	


Additional information

Certification legend



or click [here](#)

Declaration of conformity



or click [here](#)

View product online



or click [here](#)

Europe

sales@globus.com
+44 (0)161 877 4747
+44 (0)161 877 4746

Middle East & Africa

sales.gcc@globusgroup.com
+971 4 882 9962
+971 4 882 9963

Americas

salesusa@globusgroup.com
+1 83 337 54747

Globus Group, T2 Trafford Point, Twining Road, Trafford Park, Manchester, M17 1SH, UNITED KINGDOM
Globus EMEA FZE, Jafza One, Tower A, Office 2201, Jebel Ali, PO Box 61195, Dubai, UNITED ARAB EMIRATES
Globus Americas LLC, 45 Rockefeller Plaza, Suite 2000, New York City, New York, 10111, USA

The descriptions, characteristics, applications and photos are given for information purposes and do not constitute a contractual commitment.
The manufacturer reserves the right to make any modifications it deems necessary.

 **GLOBUS**