

# Product datasheet

Specifications



## Circuit breaker frame, ComPacT NS1250N, 50kA at 415VAC, 1250A, 4P, drawout, manually operated, without control unit

C125N4WM

EAN Code: 3606482098527

### Main

Range	ComPacT
Range of product	ComPacT NS630b...1600 new generation
Product or component type	Basic frame
Device application	Distribution
Number of poles	4P
Neutral position	Left
[In] rated current	1250 A at 50 °C
[Ue] rated operational voltage	690 V AC 50/60 Hz
Network type	AC
Network frequency	50/60 Hz
Suitability for isolation	Yes conforming to EN/IEC 60947-2
Utilisation category	Category B
Breaking capacity	85 kA Icu at 220/240 V AC 50/60 Hz conforming to IEC 60947-2 50 kA Icu at 380/415 V AC 50/60 Hz conforming to IEC 60947-2 50 kA Icu at 440 V AC 50/60 Hz conforming to IEC 60947-2 40 kA Icu at 500/525 V AC 50/60 Hz conforming to IEC 60947-2 30 kA Icu at 660/690 V AC 50/60 Hz conforming to IEC 60947-2
Breaking capacity code	N 50 kA 415 V AC
Control type	Manually operated
Mounting mode	Withdrawable

### Complementary

[Ui] rated insulation voltage	800 V AC 50/60 Hz conforming to IEC 60947-2
[Uimp] rated impulse withstand voltage	8 kV conforming to IEC 60947-2
[Ics] rated service breaking capacity	50 kA at 220/240 V AC 50/60 Hz conforming to IEC 60947-2 50 kA at 380/415 V AC 50/60 Hz conforming to IEC 60947-2 50 kA at 440 V AC 50/60 Hz conforming to IEC 60947-2 40 kA at 500/525 V AC 50/60 Hz conforming to IEC 60947-2 30 kA at 660/690 V AC 50/60 Hz conforming to IEC 60947-2
[Icw] rated short-time withstand current	19.2 kA 1 s conforming to IEC 60947-2
Integral instant protection	40 kA
Mechanical durability	10000 cycles conforming to IEC 60947-2
Electrical durability	2000 cycles 690 V AC 50/60 Hz In conforming to IEC 60947-2 3000 cycles 690 V AC 50/60 Hz In/2 conforming to IEC 60947-2 4000 cycles 440 V AC 50/60 Hz In conforming to IEC 60947-2 5000 cycles 440 V AC 50/60 Hz In/2 conforming to IEC 60947-2

<b>Power losses</b>	84 W
<b>Mounting support</b>	Backplate
<b>Connection pitch</b>	70 mm
<b>Protection type</b>	Without protection
<b>Height (H)</b>	327 mm
<b>Width (W)</b>	280 mm
<b>Depth (D)</b>	147 mm

## Environment

<b>Standards</b>	IEC 60947-2
<b>Product certifications</b>	IECEE CB Scheme
<b>Overvoltage category</b>	III
<b>Electrical shock protection class</b>	Class II on front face
<b>Pollution degree</b>	3 conforming to IEC 60947
<b>IP degree of protection</b>	IP40 conforming to IEC 60529
<b>IK degree of protection</b>	IK07 conforming to EN 50102
<b>Ambient air temperature for operation</b>	-25...70 °C
<b>Ambient air temperature for storage</b>	-50...85 °C

## Packing Units

<b>Unit Type of Package 1</b>	PCE
<b>Number of Units in Package 1</b>	1
<b>Package 1 Height</b>	2.0 cm
<b>Package 1 Width</b>	1.0 cm
<b>Package 1 Length</b>	2.0 cm
<b>Package 1 Weight</b>	10.0 g

## Contractual warranty

<b>Warranty (in months)</b>	18
-----------------------------	----



## Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

### Environmental footprint

Total lifecycle Carbon footprint 1811

Environmental Disclosure [Product Environmental Profile](#)

## Use Better

### Materials and Substances

Packaging made with recycled cardboard Yes

Packaging without single use plastic No

[EU RoHS Directive](#) Compliant with Exemptions

SCIP Number 3be14b62-7f55-4895-ad19-c7e3c390fbc0

REACH Regulation [REACH Declaration](#)

Halogen-free status Product contains halogen above thresholds

Silicone-free No

## Use Longer

### Lifetime extension

Repair No

## Use Again

### Repack and remanufacture

End of life manual availability [End of Life Information](#)

Take-back No

WEEE Label The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins