




Connectors > PCB Connectors > Backplane Connectors > High Speed Backplane Connectors > Backplane Connector: Plug-in module



Number of Positions: 180
Row-to-Row Spacing: 1.6 mm [.06 in]
Mating Alignment: Without
Number of Rows: 9
Number of Columns: 20

[All Backplane Connector: Plug-in module \(30\)](#)

Features

Product Type Features

Connector & Contact Terminates To	Printed Circuit Board
Connector System	Board-to-Board
PCB Connector Type	PCB Mount Header
Shroud Style	Fully Shrouded

Configuration Features

Backplane Architecture	Traditional Backplane
Number of Positions	180
Number of Rows	9
Number of Columns	20
PCB Mount Orientation	Right Angle
Guide Location	Center

Contact Features

--	--



Contact Current Rating (Max)	1.5 A
------------------------------	-------

Mechanical Attachment

Mating Alignment	Without
Connector Mounting Type	Panel Mount

Housing Features

Number of Shrouded Sides	4
Centerline (Pitch)	.08 mm[1.9 in]

Dimensions

Row-to-Row Spacing	1.6 mm[.06 in]
--------------------	----------------

Usage Conditions

Operating Temperature Range	-65 – 125 °C[-85 – 257 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Signal
---------------------	--------

Product Compliance

For compliance documentation, visit the product page on TE.com>


EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2024 (240) Does not contain REACH SVHC
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>




Customers Also Bought




TE Part #1735482-3
0.8FH,R17H.5,080,08/Sn,TR,SC




TE Part #8-1622796-9
YR1 0.1% 191K




TE Part #9-1734774-3
PCI EXP 2.3L 64 POS BLK 30u"




TE Part #1-1879208-4
CPF 0402 36R 0.1% 25PPM 1K RL




TE Part #861647-6
RECPT FLANGED H.V. 7 CONTACTS




TE Part #1735482-4
0.8FH,R17H.5,100,08/Sn,TR,SC




TE Part #4-2176230-7
3522 5K6 5% 3W



TE Part #8-1879160-5
RN 0805 8R66 0.1% 10PPM 1K RL



TE Part #1376073-2
DYNAMIC D-2000 TAB ASSY 50P



TE Part #50865
SOCKET,MIN-SPR AU SER-4

Documents

Product Drawings
Fortis Zd 3Pr 20Col R/A Full Shrd Assy
English

CAD Files
3D PDF
3D
Customer View Model
ENG_CVM_CVM_2102159-2_B.2d_dxf.zip
English
Customer View Model
ENG_CVM_CVM_2102159-2_B.3d_igs.zip
English
Customer View Model
ENG_CVM_CVM_2102159-2_B.3d_stp.zip
English



By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Fortis Zd LRM

English

Product Specifications

Application Specification

English